



YAGB25LTC38FXOEM, Battery Terminal, 1/0 AWG, 1-Hole, 3/8" Stud

By Burndy

Catalog # [YAGB25LTC38FXOEM](#)

1/0 AWG, 3/8 Stud Size, One Hole Cu Battery Terminal



Features

- Color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliant	Yes
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	1/0 AWG
Conductor - Copper Flex K Size Range	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Conductor - Copper Flex M Size	1/0 AWG
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Flex I Size Range	1/0 AWG
Conductor - Copper Flex G Size	1/0 AWG
Conductor - Copper DLO Size Range	1/0 AWG
Conductor - Copper DLO Size	1/0 AWG
Conductor Size	1/0 AWG
Conductor - Copper Flex H Size	1/0 AWG
Conductor - Copper Flex G Size Range	1/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	1/0 AWG

Conductor - Copper Flex H Size 1/0 AWG Range

Conductor - Copper Flex I Size 1/0 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	GROUNDING/STARTER LUGS

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.93 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	49 mm
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.38 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	1.93 in

General

Trade Name	HYLUG™
Die Index	12
Color Code	Pink
Sub Brand	HYLUG
UPC	781810547434
Type	OEM Terminals
Construction Material - Main Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Electro Tin plated

UPC 12 Digit	781810547434	Pallet Quantity	16400
UPC 14 Digit GTIN	00781810547434	Carton Quantity	200

Logistics

Minimum Pack Quantity 200



A Hubbell brand

Product Assets

[Catalog \[English\]](#)