



YAE12N1, Nylon Ring, 14-12 AWG, #6-8 Stud

By Burndy

Catalog # [YAE12N1](#)

Nylon Ring Terminal For 14 - 12 AWG, #6-8 Stud, Multi-Finger Insulation Grip, Deep V Groove, Bulk Package



Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulation
- Brazed seam for a strong, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability, and holding power
- Smooth funnel entry for easy wire insertion

Application

For use on copper compression connections

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	14 - 12 AWG
Conductor - Copper Str Aircraft Size	• AN 14 • AN 12
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 12 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	8/47
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	27 mm
Dimension - Hole Size inch	0.17 in
Dimension - Strip Length inch	21/64 in
Dimension - Stud Size inch	#6 - #8
Dimension - Bolt Size fraction	#6 - #8
Dimension - Z inch	0.286 in
Dimension - N inch	0.16 in
Dimension - Length Overall inch	1.06 in

General

Product Family	COMPRESSION
Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Shrouded
Plated	Yes
Color Code	Green
Physical Attribute - Tongue Type	Ring Terminal
Sub Brand	INSULUG
Product Type	Terminal
UPC	781810804421
Type	YAE-N
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810804421
UPC 14 Digit GTIN	00781810804421

Logistics

Minimum Pack Quantity	500
Pallet Quantity	99999
Carton Quantity	500

Operational

Temperature Rating	105° C
--------------------	--------

Product Assets

[Catalog \[English\]](#)



A Hubbell brand