



YAGB28LTC38FX, Battery Terminal, 4/0 AWG, 1-Hole, 3/8" Stud

By Burndy

Catalog # [YAGB28LTC38FX](#)

4/0 AWG, 3/8 Stud Size, One Hole Cu Battery Terminal



Features

- Color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper DLO Size Range	4/0 AWG
Conductor - Copper DLO Size	4/0 AWG
Conductor Size	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex G Size Range	4/0 AWG
Conductor - Material	COPPER
Wire Size	4/0 AWG
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex I Size Range	4/0 AWG

Configuration

Connector Type	GROUNDING/STARTER LUGS
----------------	------------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.10 in
Package Height	2.600 in
Dimension - Hole Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Package Weight	2.660 lb.
Package Length	5.200 in
Package Width	3.250 in
Dimension - Z inch	0.48 in
Dimension - L Length Overall mm	65 mm
Dimension - Outside Diameter inch	.78 In
Dimension - N inch	0.55 in
Dimension - Hole Size mm	10.4 mm
Dimension - Bolt Size inch	0.38
Dimension - Hole Size inch	0.41
Dimension - Length Overall inch	2.56 in
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size inch	3/8 in
Dimension - Stud Size fraction	3/8

General

Plated	Y
Color Code	Purple
Trade Name	HYLUG™
Die Index	15
UPC	781810562925
Type	OEM Terminals
Material	COPPER
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810562925
UPC 14 Digit GTIN	00781810562925

Logistics

Pallet Quantity	12000
Carton Quantity	200



A Hubbell brand

Product Assets

[Catalog \[English\]](#)