




YAGB2CLTC12FXOEM, Battery Terminal, 2 AWG, 1-Hole, 1/2" Stud

By Burndy

Catalog # [YAGB2CLTC12FXOEM](#)

2 AWG, 1/2 Stud Size, One Hole Cu Battery Terminal



Features

- Color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliant	Yes
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Size	2 AWG
Conductor - Copper DLO Size	2 AWG
Range	
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex G Size	2 AWG
Range	
Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size	2 AWG
Range	
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	2 AWG
Range	
Conductor - Copper Str Size	2 AWG
Conductor - Copper Flex H Size	2 AWG
Range	
Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex I Size	2 AWG
Range	

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	GROUNDING/STARTER LUGS

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.81 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	53 mm
Dimension - Hole Size mm	13.5 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.53
Dimension - Length Overall inch	2.09 in
Dimension - Strip Length inch	15/16 in
Dimension - Stud Size inch	1/2 in
Dimension - Stud Size fraction	1/2

General

Color Code	Brown
Trade Name	HYLUG™
Die Index	10
UPC	781810547465
Type	OEM Terminals
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810547465
UPC 14 Digit GTIN	00781810547465

Logistics

Minimum Pack Quantity	200
-----------------------	-----

Pallet Quantity	1	Temperature Rating	194
Carton Quantity	1		

Operational

Product Assets

[Catalog \[English\]](#)



A Hubbell brand