




YAE22N66FNK, Nylon Fork Terminal For 26 - 20 AWG (Nickel Plated)

By Burndy
Catalog # [YAE22N66FNK](#)

Nylon Fork Terminal For 26 - 20 AWG (Nickel Plated)



Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulations
- Brazed seams for a stronger, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability, and holding power
- Smooth funnel entry for easy wire insertion

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
Industry Standard(s)	Military Specified (Mil-Spec)
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Aircraft Size	• AN 26 • AN 22 • AN 20
Conductor Size	26 - 20 AWG
Conductor - Copper Str Size Range	24 AWG - 20 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Fork Terminal
----------------	---------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	10/91 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.11 in
Dimension - Z inch	0.27 in
Dimension - Pad Width inch	0.28 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/20
Dimension - Bolt Size fraction	#4 - #6
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	5/32 in
Dimension - Stud Size inch	• #4 • #5 • #6
Dimension - Length Overall inch	0.8 in
Dimension - N inch	0.12 in

General

Insulation Type	Nylon
Color Code	Amber
Physical Attribute - Tongue Type	Fork
Trade Name	INSULUG™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation	Y
UPC 12 Digit	781810218587
UPC 14 Digit GTIN	00781810218587
Material	Copper
Plating Type	Nickel
UPC	781810218587

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)