



Cu T-Type Battery Post Conn, 1 AWG, Negative, Tinned, Bulk

By Burndy

Catalog # [YAEBAFICNTNOEM](#)

1 AWG, NEGATIVE T-STYLE BATTERY POST TERMINAL



Features

- Barrel is color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Supplied standard with stainless steel hardware installed
- Clamp color coded by polarity - Red is Postive, Black is Negative
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Battery Post Terminal

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliant	Yes
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Size	1 AWG
Conductor - Copper Str Compact Size	1 AWG
Conductor - Copper DLO Size	1 AWG
Conductor Size	1 AWG
Conductor - Copper Flex H Size	1 AWG
Conductor - Material	COPPER
Wire Size	1 AWG
Conductor - Copper Flex K Size	1 AWG
Conductor - Copper Flex M Size	1 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	1 AWG
Conductor - Copper Str Size	1 AWG
Conductor - Copper Flex I Size	1 AWG

Configuration

Connector Type	BATTERY T-POST
----------------	----------------



A Hubbell brand

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.36 in

Force Related

Installation Torque Recommended in-lb	72 LBS/in
---------------------------------------	-----------

General

Plated	Y
Color Code	Green
Trade Name	HYLUG™
Die Index	11
UPC	781810566237
Type	OEM Terminals
Material	Copper
Plating Type	Tin Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810566237
UPC 14 Digit GTIN	00781810566237

Logistics

Minimum Pack Quantity	200
Pallet Quantity	1
Carton Quantity	1

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)