



# YAS25RN, Aluminum - Compression Stacking Terminal (HYLUG Terminal)

By Burndy  
Catalog # [YAS25RN](#)

Aluminum Stacking Terminal- Straight Lug, 1/0 Al-Cu, 1/0 ACSR, 1 Hole, Yellow

## Features

- Aluminum Stacking Terminal- Straight Lug,1/0 Al-Cu, 1/0 ACSR
- 1 Hole

## Specifications

|                                    |    |
|------------------------------------|----|
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Standards - RoHS Compliance Status | CM |
| Certification - cULus              | No |
| UL Listed                          | No |
| Certification - CSA Approved       | No |

## Conductor

|                                   |                     |
|-----------------------------------|---------------------|
| Conductor - AL Str Size           | 1/0 AWG             |
| Conductor - AL Str Size Range     | 1/0 AWG             |
| Conductor - ACSR Str Size         | 1/0 (6/1) Raven AWG |
| Conductor - Copper Str Size Range | 1/0 AWG             |
| Conductor - Copper Str Size       | 1/0 AWG             |
| Conductor - ACSR Str Size         | 1/0 (6/1) Raven AWG |

## Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Pad Width inch      | 0.90 in |
| Dimension - Z inch              | 1.10 in |
| Dimension - P inch              | 1.29 in |
| Dimension - L Length Overall mm | 77 mm   |
| Dimension - B Length inch       | 0.96 in |



|                                   |           |
|-----------------------------------|-----------|
| Dimension - Outside Diameter inch | 0.65 in   |
| Dimension - N inch                | 0.63 in   |
| Dimension - Inside Diameter inch  | 0.42 in   |
| Dimension - Hole Size inch        | 0.56 in   |
| Dimension - Length Overall inch   | 3.05 in   |
| Dimension - Strip Length inch     | 1-3/32 in |

## General

|                        |                                                                                              |
|------------------------|----------------------------------------------------------------------------------------------|
| Feature - Barrel Style | Chamfered                                                                                    |
| Plated                 | N                                                                                            |
| Color Code             | Yellow                                                                                       |
| Trade Name             | HYLUG™                                                                                       |
| Die Index              | <ul style="list-style-type: none"><li>BG</li><li>243</li><li>K-5/8-1</li><li>CSA22</li></ul> |
| UPC                    | 781810093931                                                                                 |
| Material               | Aluminum                                                                                     |
| Plating Type           | Unplated                                                                                     |
| UPC 12 Digit           | 781810093931                                                                                 |
| UPC 14 Digit GTIN      | 00781810093931                                                                               |

## Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 20    |
| Pallet Quantity       | 19200 |
| Carton Quantity       | 20    |

## Product Assets

[Catalog \[English\]](#)