

YAV630F2M16, Compression Terminal

By Burndy
Catalog # [YAV630F2M16](#)

Cu Compression Metric Lug, 2 Hole, W/Inspection Window, 630 mm, M16 Stud, 44.5 mm Spacing, Standard Barrel, 55 mm Wire Strip Length.

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive
- Compatible Standards: IEC61238-1, UL 486A-486B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

General

Catalog Number	YAV630F2M16
Connector Type	METRIC
Die Index	31
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810641170
UPC 14 Digit GTIN	00781810641170

Dimensions

Dimension - B Length inch	2.00 in
Dimension - Bolt Size fraction	5/8
Dimension - Bolt Size inch	0.63
Dimension - Hole Size fraction	5/8
Dimension - Hole Size inch	0.69
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	161 mm
Dimension - Length Overall inch	6.35 in



Dimension - Pad Width inch	2.69 in
Dimension - Strip Length inch	2.17 in
Dimension - Stud Size fraction	5/8
Dimension - Z (inch)	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Material	COPPER
Conductor Size	630 mm2
Conductor Type	CLASS 2

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

- [3D Models - YAV630F2M16_MODEL-IGES](#)
- [3D Models - YAV630F2M16_MODEL-STEP](#)
- [3D Models - YAV630F2M16_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
- [Sales Drawings - 50025888](#)
- [Specifications - YAV630F2M16](#)