



YAGB4CLTC516FX, Battery Terminal, 4 AWG, 1-Hole, 5/16" Stud

By Burndy
Catalog # [YAGB4CLTC516FX](#)

4 AWG, 5/16 Stud Size, One Hole Cu Battery Terminal



Features

- Color coded for easy identification
- Chamfered end
- Made of copper alloy, tin plated for corrosion resistance and RoHS compliance
- Not UL Listed but tested and met UL486A-486B pullout requirements

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Size	4 AWG
Conductor - Copper DLO Size Range	4 AWG
Conductor - Copper DLO Size	4 AWG
Conductor Size	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex G Size Range	4 AWG
Conductor - Material	COPPER
Wire Size	4 AWG
Conductor - Copper Flex K Size Range	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor - Copper Flex H Size Range	4 AWG
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex I Size Range	4 AWG

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	GROUNDING/STARTER LUGS

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.75 in
Package Height	1.900 in
Dimension - Hole Size fraction	5/16
Dimension - Bolt Size fraction	5/16
Physical Attribute - Tongue Angle	Straight
Package Weight	0.860 lb.
Package Length	3.400 in
Package Width	2.600 in
Dimension - L Length Overall mm	50 mm
Dimension - Hole Size mm	10 mm
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size inch	0.38
Dimension - Length Overall inch	1.97 in
Dimension - Strip Length inch	15/16 in
Dimension - Stud Size inch	5/16 in
Dimension - Stud Size fraction	5/16

General

Color Code	Gray
Trade Name	HYLUG™
Die Index	6
UPC	781810562741
Type	OEM Terminals
Material	Copper
Finish Type	Tin-Plated
UPC 12 Digit	781810562741
UPC 14 Digit GTIN	00781810562741

Logistics

Minimum Pack Quantity	20
Pallet Quantity	33000

Carton Quantity200

Product Assets

Operational

Catalog [\[English\]](#)

Temperature Rating194



A Hubbell brand