




YAZ27TC12. Compression Terminal, 3/0 AWG Cu, 1-Hole, 1/2" Stud, Long Barrel

By Burndy

Catalog # [YAZ27TC12](#)

3/0 AWG, CU, 1 Hole, 1/2 Stud, Long Barrel, Inspection Window



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	3/0 AWG
Conductor Size	3/0 AWG
Conductor - Copper Str Navy Size Range	150 (61) Navy
Conductor - Copper Str Navy Size	150 (61) Navy
Conductor Type	CODE

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.90 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	77 mm
Dimension - Outside Diameter inch	0.62 in
Dimension - Hole Size mm	13.5 mm
Dimension - Hole Size inch	0.53
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.55 in
Dimension - B Length inch	1.50 in
Dimension - N inch	0.53 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	3.04 in

General

Trade Name	HYLUG™
Die Index	14
Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Yes
Color Code	Orange
Sub Brand	HYLUG
UPC	781810240083
Type	YAZ, Code Conductor Long Barrel
Construction Material - Main Material	Copper tubing Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810240083
UPC 14 Digit GTIN	00781810240083

Logistics

Minimum Pack Quantity	1
Pallet Quantity	24000
Carton Quantity	25

Product Assets

- Catalog [English]
- Installation Manual [English]
- Installation Manual [French, English]



A Hubbell brand