



YAV16M12, Compression Terminal

By Burndy

Catalog # [YAV16M12](#)

Copper Compression Terminal



Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping
- Compatible Standards: IEC61238-1, UL 486A-486B, CSA-C22.2 No. 65-03

Application

Metric Wire Termination

Specifications

Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	16 mm2
Conductor - Copper DLO Size Range	N/A
Conductor Size	16 mm2
Conductor Type	CLASS 2

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	METRIC

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.74 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall mm	41.6 mm
Dimension - Outside Diameter inch	0.31 in
Dimension - Hole Size mm	13.5 mm
Dimension - Hole Size inch	0.53
Dimension - Strip Length inch	0.51 in
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.22 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - Z inch	0.49 in
Dimension - B Length inch	0.50 in
Dimension - N inch	0.47 in
Dimension - Inside Diameter inch	0.22 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	0.05 in

General

Trade Name	HYLUG™
Die Index	7
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	YES
Physical Attribute - Tongue Type	Ring
UPC	781810286012
Type	Metric Terminals
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810286012
UPC 14 Digit GTIN	00781810286012

Logistics

Minimum Pack Quantity	50
Pallet Quantity	99999
Carton Quantity	200

Product Assets

[Catalog \[English\]](#)



A Hubbell brand