

YC2A2, Aluminum C-Shape Connector

By Burndy
Catalog # [YC2A2](#)

Range-taking, C-shaped AL compression tap, or dead-ending connector designed to eliminate the effects of cold flow, 1-1/2" L, Run(Aluminum):2 Sol. & Str.

Features

- Range-taking C-shaped aluminum compression tap, or dead-ending connector, designed to eliminate effects of cold flow
- Connector can be gripped in tool and slipped over line for easy crimping
- Pre-filled with PENETROX joint compound and strip sealed

Application

For Combinations Of Aluminum, ACSR, 6201, 5005, Compressed and Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	4 AWG-2 AWG
Conductor - ACSR Cmpt Run	• 4 AWG • 3 AWG • 2 AWG
Conductor - AAAC 5005 Tap Range	48.69 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 5005 Tap	• 48.69 (7) kcmil • 77.47 (7) kcmil
Conductor - AAAC 6201 Run Range	48.69 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 6201 Run	• 48.69 (7) kcmil • 77.47 (7) kcmil
Conductor - AAAC 6201 Tap Range	48.69 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 6201 Tap	• 48.69 (7) kcmil • 77.47 (7) kcmil
Conductor - AL Str Run Range	2 Sol. - 2 Str
Conductor - AL Str Run	2 AWG
Conductor - AL Str Tap Range	2 Sol. - 2 Str.
Conductor - AL Str Tap	2 AWG
Conductor - ACSR Cmpt Tap Range	4 AWG-2 AWG
Conductor - ACSR Cmpt Tap	• 4 AWG



Conductor - ACSR Str Run Range	• 3 AWG • 2 AWG
Conductor - ACSR Str Tap Range	4 AWG - 2 AWG
Conductor - AAAC 5005 Run Range	4 AWG - 2 AWG
Conductor - AAAC 5005 Run	48.69 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 5005 Run	• 48.69 (7) kcmil • 77.47 (7) kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	1.00 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	38 mm
Width	1 in
Length	1.5 in
Height	1.5 in
Dimension - Length Overall inch	1.50 in
Dimensions	1.5 in x 1 in x 1.5 in

General

Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>C-Taps
Trade Name	CRIMPIT™
Die Index	C
Plated	No
Sub Brand	CRIMPIT
Product Type	Compression
UPC	781810121504
Type	YC-A
Construction Material - Main Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810121504
UPC 14 Digit GTIN	00781810121504

Logistics

Minimum Pack Quantity	100
Pallet Quantity	24000
Carton Quantity	100



A Hubbell brand