



# YCA4R2N, Al compression lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing, #4

By Burndy  
Catalog # [YCA4R2N](#)

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 5.6 IN L

## Features

- Aluminum Compression Lug
- 2-Hole, 1/2" Stud, 1-3/4" Spacing

## Specifications

|                                    |                                                     |
|------------------------------------|-----------------------------------------------------|
| Certification - cULus              | No                                                  |
| Certification - UL Recognized      | No                                                  |
| Buy America(n) Qualified           | TAA Compliant (All status valid till December 2026) |
| Certification - ETL                | No                                                  |
| Standards - RoHS Compliance Status | CM                                                  |
| Certification - CSA Approved       | No                                                  |
| UL Listed                          | No                                                  |

## Conductor

|                                 |                   |
|---------------------------------|-------------------|
| Conductor - ACSR Str Size       | #4 (6/1) Swan AWG |
| Conductor - ACSR Str Size Range | 4 (6/1) Swan AWG  |
| Conductor - AL Str Size         | 4 AWG             |
| Conductor - AL Str Size Range   | 4 AWG             |

## Configuration

|                                        |             |
|----------------------------------------|-------------|
| Physical Attribute - Pad Configuration | 2 Hole NEMA |
| Connector Type                         | Terminal    |

## Dimensions

|                |          |
|----------------|----------|
| Package Length | 0.000 in |
|----------------|----------|

|                                              |           |
|----------------------------------------------|-----------|
| Dimension - E Spacing between Holes fraction | 1-3/4 in  |
| Package Width                                | 0.000 in  |
| Package Weight                               | 0.000 lb. |
| Dimension - L Length Overall mm              | 143 mm    |
| Dimension - Pad Width inch                   | 1.25 in   |
| Package Height                               | 0.000 in  |
| Dimension - B Length inch                    | 1.61 in   |
| Dimension - Bolt Hole Size inch              | 0.56 in   |
| Dimension - Length Overall inch              | 5.66 in   |

## General

|                           |                |
|---------------------------|----------------|
| Die Index                 | 237            |
| Trade Name                | HYLUG™         |
| Prefilled Oxide Inhibitor | Y              |
| Plated                    | N              |
| UPC 12 Digit              | 781810016640   |
| UPC 14 Digit GTIN         | 00781810016640 |
| Material                  | Aluminum       |
| Plating Type              | Unplated       |
| UPC                       | 781810016640   |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 6 |
| Carton Quantity       | 1 |
| Pallet Quantity       | 1 |

## Product Assets

[Catalog \[English\]](#)