



YCB38R26U, CRIMPIT™ Series Hot Tap,
336.4 kcmil (26/7), 556.5 (18/1) kcmil
ACSR, 397.5 kcmil 600(61) kcmil Cu or Al

By Burndy
Catalog # [YCB38R26U](#)



CRIMPIT™ HOT TAP, 336.4 kcmil(26-7), 556.5(18-1) kcmil ACSR,
397.5(19) kcmil-600(61) kcmil Cu or Al

Features

- Combines Figure 6-Shaped aluminum CRIMPIT Tap Connector with Tin-Plated Copper Bail
- Can be gripped in tool and slipped over line for easy installation
- Prefilled with PENETROX Joint Compound and stripsealed

Application

For Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil
Conductor - AL Str Size Range	397 kcmil - 600 kcmil
Conductor - ACSR Str Size	• 336.4 (26/7) Linnet kcmil • 336.4 (30/7) Oriole kcmil • 397.5 (18/1) Chickadee kcmil • 397.5 (24/7) Brant kcmil • 397.5 (26/7) Ibis kcmil • 397.5 (30/7) Larkspur kcmil • 477.0 (18/1) Pelican kcmil • 477.0 (24/7) Flicker kcmil • 477.0 (26/7) Hawk kcmil

Conductor - ACSR Str Size
Range

- 477. (30/7) Hen kcmil
 - 500.0 (30/7) Heron kcmil
 - 556.5 (24/7) Parakeet kcmil
- 336.4 (26/7) Linnet kcmil-556.5 (24/7) Parakeet kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	57.2 mm
Dimension - Height inch	2.28 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	54 mm
Dimension - Bail Size	0.325 in
Dimension - Length Overall inch	2.12 in

General

Trade Name	CRIMPIT™
Die Index	N
Prefilled Oxide Inhibitor	N
Plated	N
Sub Brand	CRIMPIT
Series	CRIMPIT™ Series
UPC	781810014110
Type	Stirrups
Material	Aluminum
Material - Bail	Copper
Plating Type	Unplated
UPC 12 Digit	781810014110
UPC 14 Digit GTIN	00781810014110

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)



A Hubbell brand