




YCHC2TC2, Compression C-Tap

By Burndy

Catalog # [YCHC2TC2](#)



Copper Compression C Tap, 2-6 AWG (Main), 2-6 AWG (Tap 1), 8-14 AWG (Tap 2), Tin Plated

Features

- Range taking C-tap that allows for less inventory as one C-tap can accommodate a multitude of wire combinations
- Manufactured from high conductivity wrought copper providing low resistance for excellent electrical conductivity
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Tap Range	8 AWG-2 AWG
Conductor - Copper Flex M Run Range	8 AWG-2 AWG
Conductor - Copper Flex I Tap Range	8 AWG-2 AWG
Conductor - Copper Flex K Run Range	8 AWG-2 AWG
Conductor Size	2 AWG-2 AWG
Conductor - Copper Str Run Range	2 AWG-6 AWG
Conductor - Copper Str Run Range	2 AWG-6 AWG
Conductor - Copper Flex M Tap Range	8 AWG-2 AWG
Conductor - Copper Solid Run	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

Conductor - Copper Solid Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex I Run Range	8 AWG-2 AWG
Conductor - Copper Str Tap Range	2 AWG-6 AWG
Conductor - Copper Str Tap	2 AWG-6 AWG

Configuration

Connector Type	C-TAP
----------------	-------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height inch	1.22 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	21 mm
Dimension - Strip Length inch	1 in
Dimension - Width inch	0.6 in
Dimension - Length Overall inch	0.81 in

General

Trade Name	CRIMPIT™
Die Index	C
Plated	Y
Color Code	Brown
Sub Brand	CRIMPIT
UPC	781810013816
Type	YCHC Series
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810013816
UPC 14 Digit GTIN	00781810013816

Logistics

Minimum Pack Quantity	1
Pallet Quantity	29600

Carton Quantity100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand