


YCHC44TC44, Compression C-Tap

By Burndy

Catalog # [YCHC44TC44](#)

Copper Compression C Tap, 1000-750 kcmil (Main), 1000-750 kcmil (Tap), Tin Plated



Features

- Range taking C-tap that allows for less inventory as one C-tap can accommodate a multitude of wire combinations
- Manufactured from high conductivity wrought copper providing low resistance for excellent electrical conductivity
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Tap Range	800 kcmil-1000 kcmil
Conductor - Copper Flex M Run Range	800 kcmil-1000 kcmil
Conductor - Copper Flex I Tap Range	800 kcmil-1000 kcmil
Conductor - Copper Flex K Run Range	800 kcmil-1000 kcmil
Conductor Size	1000 KCMIL-1000 KCMIL
Conductor - Copper Str Run Range	1000 KCMIL-750 KCMIL
Conductor - Copper Str Run	1000 KCMIL-750 KCMIL
Conductor - Copper Flex M Tap Range	800 kcmil-1000 kcmil
Conductor Type	CODE/FLEX
Conductor - Copper Flex I Run Range	800 kcmil-1000 kcmil
Conductor - Copper Str Tap Range	1000 KCMIL-750 KCMIL

Conductor - Copper Str Tap 1000 KCMIL-750 KCMIL

Configuration

Connector Type C-TAP

Current

Voltage - Maximum 35000

Dimensions

Package Height	0.000 in
Dimension - Height inch	3.59 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	29 mm
Dimension - Strip Length inch	1-1/4
Dimension - Width inch	1.73 in
Dimension - Length Overall inch	1.16 in

General

Trade Name	CRIMPIT™
Die Index	1102
Plated	Y
Color Code	White
UPC	781810013748
Type	YCHC Series
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810013748
UPC 14 Digit GTIN	00781810013748

Logistics

Minimum Pack Quantity	25
Pallet Quantity	2400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)