

YCR30RG4, Compression reducer for Copper/ACSR

By Burndy
Catalog # [YCR30RG4](#)



HYSPLCE REDUCER(CU-ACSR)

Features

- Copper Reducer for Copper/Reducer

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	300
Conductor - Copper Str Size B	1/0
Conductor - Copper Str Size A	300
Range	
Conductor - ACSR Cmpt Size A	• 266.8 (26/7) Owl • 266.8 (26/7) Partridge
Conductor - AAAC 5005 Size B	123.3 (7)
Conductor - AAAC 5005 Size A	312.8 (19)
Range	
Conductor - AAAC 5005 Size B	123.3 (7)
Range	
Conductor - AAAC 6201 Size B	312.8 (19)
Range	
Conductor - AAAC 6201 Size A	312.8 (19)
Conductor - AAAC 6201 Size B	123.3 (7)
Conductor - AAAC 6201 Size A	312.8 (19)
Range	
Conductor - AL Str Size A	• 300 • 336.4
Conductor - AL Str Size B	1/0
Conductor - AL Str Size A	300-336.4
Range	
Conductor - AAAC 5005 Size A	312.8 (19)
Conductor - AL Str Size B	1/0
Range	
Conductor - ACSR Str Size A	266.8 (26/7) Owl kcmil
Conductor - ACSR Str Size B	1/0 (6/1) Raven

Conductor - ACSR Str Size A	266.8 (26/7) Owl kcmil
Range	
Conductor - Copper Str Size B	1/0
Range	
Conductor - ACSR Str Size B	1/0 (6/1) Raven
Range	

Configuration

Connector Type	Reducer
----------------	---------

Dimensions

Dimension - B Length fraction	3 in
Dimension - L Length Overall	187 mm
mm	
Dimension - B Length inch	3 in
Dimension - Outside Diameter	1.25 in
inch	
Dimension - Length Overall	7.38 in
inch	
Dimension - Strip Length inch	3 1/16

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 705 • 317
Oxide Inhibitor Type	Penetrox A
UPC	781810324592
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810324592

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1960
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)