



YC6L12, Cu Compression C-Tap, Thin Wall

By Burndy
Catalog # YC6L12

Copper Compression C Tap, Thin Wall, 8 AWG (Run), 10-8 AWG (Tap)



Features

- Material is high conductivity wrought copper providing low resistance for excellent electrical conductivity
- Bare copper range taking connector allows for less inventory
- Reinforced ribs on the outside of the connector increase the mechanical strength of the connection
- Creates a compact connection that is easy for taping and insulating
- Connectors are clearly marked with color code dot, UL and CSA (when applicable), wire size, and die index number

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	Yes
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	• Buy America Compliant (All status valid till December 2026) • Buy American Act Compliant (All status valid till December 2026) • BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor Size	6 AWG-12 AWG
Conductor - Copper Str Run Range	6 AWG-8 AWG
Conductor - Copper Str Run	6 AWG-8 AWG
Conductor Type	CODE
Conductor - Copper Str Tap Range	8 AWG-12 AWG

Conductor - Copper Str Tap 8 AWG-12 AWG

Configuration

Physical Attribute - Number of	2
Crimps Required	
Connector Type	C-TAP

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.25 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Strip Length inch	5/8
Dimension - B Length fraction	5/16 in
Dimension - B Length inch	0.33 in
Dimension - D inch	0.60 in

General

Trade Name	CRIMPIT™
Die Index	8
Plated	Y
Color Code	Gray
Sub Brand	CRIMPIT
UPC	781810040126
Type	YC-L Series
Material	Copper
Plating Type	Tin - Bright
Finish Type	Tin-Plated
UPC 12 Digit	781810040126
UPC 14 Digit GTIN	00781810040126

Logistics

Minimum Pack Quantity	1
Pallet Quantity	96000
Carton Quantity	100

Operational

Temperature Rating	194
--------------------	-----



A Hubbell brand