

YCA33R2N, Al Compression Lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCA33R2N](#)

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 7.29 IN L

Features

- Aluminum compression HYLUG
- NEMA Standard Mounting Holes

Application

Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends.

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - AAAC 5005 Size Range	394.5 (19) kcmil
Conductor - AAAC 6201 Size	394.5 (19) kcmil
Conductor - AAAC 6201 Size Range	394.5 (19) kcmil
Conductor - ACSR Str Size	336.4 (26/7) Linnet kcmil 336.4 (30/7) Oriole kcmil
Conductor - ACSR Str Size Range	336.4 (26/7) Linnet kcmil-336.4 (30/7) Oriole kcmil
Conductor - AL Str Size	397.5 (19) Kcmil
Conductor - AAAC 5005 Size	394.5 (19) kcmil

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
--	-------------



Connector Type	Terminal
----------------	----------

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	1.14 in
Dimension - L Length Overall mm	185 mm
Dimension - Pad Width inch	1.60 in
Package Height	0.000 in
Dimension - B Length inch	3.00 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - Length Overall inch	7.29 in

General

Die Index	316
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Plated	N
Type	YCA-R-N
UPC 12 Digit	781810016664
UPC 14 Digit GTIN	00781810016664
Material	Aluminum
Plating Type	Unplated
UPC	781810016664

Logistics

Minimum Pack Quantity	1
Carton Quantity	40
Pallet Quantity	3920

Product Assets

[Catalog \[English\]](#)