

YCB2R, Al Stirrup Connector, hot-line clamp adapter with Al run and Cu bail

By Burndy
Catalog # [YCB2R](#)



Stirrup Connector, Aluminum: 4(Str.)AWG, 2(Str.)AWG, 2(Sol.)AWG, ACSR: 2(6/1)AWG, 2(7/1)AWG, 4(6/1)AWG, 4(7/1)AWG

Features

- Permanent compression hot-line clamp adapter with aluminum run and copper bail
- Accommodates any standard copper hotline clamp on bail elements
- Permits hotline tapping without arcing or chafing damage to aluminum conductor
- Installed with standard tools and dies

Application

For Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 4 AWG • 2 AWG
Conductor - AL Str Size Range	4 AWG-2 AWG
Conductor - ACSR Str Size	• 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	4 (6/1) Swan AWG-2 (7/1) Sparate AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	95.3 mm
Dimension - Height inch	3.75 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	2.50 in
Package Width	0.000 in
Dimension - L Length Overall mm	227 mm
Dimension - Width mm	18 mm
Dimension - Width inch	0.72 in
Dimension - Bail Size	0.25 in
Dimension - D inch	2.50 in
Dimension - Length Overall inch	8.95 in

General

Die Index	BG
Prefilled Oxide Inhibitor	N
Plated	N
Sub Brand	CRIMPIT
UPC	781810151501
Type	Stirrups
Material	Aluminum
Material - Bail	Copper
Plating Type	Unplated
UPC 12 Digit	781810151501
UPC 14 Digit GTIN	00781810151501

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3000
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)