



YCHC39TC39, Compression C-Tap

By Burndy

Catalog # [YCHC39TC39](#)

Copper Compression C Tap, 750-500 kcmil (Main), 750-350 kcmil (Tap), Tin Plated



Features

- Range taking C-tap that allows for less inventory as one C-tap can accommodate a multitude of wire combinations
- Manufactured from high conductivity wrought copper providing low resistance for excellent electrical conductivity
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Tap Range	350 kcmil-500 kcmil
Conductor - Copper Flex M Run Range	500 kcmil
Conductor - Copper Flex I Tap Range	350 kcmil-500 kcmil
Conductor - Copper Flex K Run Range	500 kcmil
Conductor Size	750 KCMIL-750 KCMIL
Conductor - Copper Str Run Range	750 KCMIL-350 KCMIL
Conductor - Copper Str Run	750 KCMIL-350 KCMIL
Conductor - Copper Flex M Tap Range	350 kcmil-500 kcmil
Conductor Type	CODE/FLEX
Conductor - Copper Flex I Run Range	500 kcmil
Conductor - Copper Str Tap Range	750 KCMIL-350 KCMIL

Conductor - Copper Str Tap750 KCMIL-350 KCMIL

Configuration

Connector TypeC-TAP

Current

Voltage - Maximum35000

Dimensions

Package Height	0.000 in
Dimension - Height inch	3.12 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	27 mm
Dimension - Strip Length inch	1-1/8
Dimension - Width inch	1.53 in
Dimension - Length Overall inch	1.06 in

General

Trade Name	CRIMPIT™
Die Index	1103
Insulation	N
Plated	Y
Color Code	Blue
Sub Brand	CRIMPIT
UPC	781810013793
Type	YCHC
Construction Material - Main Material	Copper Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810013793
UPC 14 Digit GTIN	00781810013793

Logistics

Minimum Pack Quantity	15
Pallet Quantity	3330
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)



A Hubbell brand