




# YCU28R, Aluminum Repair Sleeve

By Burndy  
Catalog # [YCU28R](#)

Cast AL repair sleeve for restoring conductivity to damaged conductor, 11-7/8 IN L



## Features

- For restoring conductivity to damaged conductors
- Made of cast aluminum, sizes up through 266.8 kcmil are U-Shaped
- for 300 kcmil and larger, sleeves are 2-Piece Interlocking elements
- Use of PENETROX Joint Compound Required

## Application

For ACSR and Compressed And Compact Conductors

## Specifications

|                               |                      |
|-------------------------------|----------------------|
| Buy American Compliant        | Contact Manufacturer |
| Certification - cULus         | No                   |
| EU RoHS Indicator             | Yes                  |
| Certification - UL Recognized | No                   |
| Buy America(n) Qualified      | Contact Manufacturer |
| Certification - ETL           | No                   |
| Standards - RoHS Compliance   | CM                   |
| Status                        |                      |
| Certification - CSA Approved  | No                   |
| UL Listed                     | No                   |

## Conductor

|                                  |                                               |
|----------------------------------|-----------------------------------------------|
| Conductor - ACSR Cmpt Size       | 4/0 AWG                                       |
| Conductor - ACSR Cmpt Size Range | 4/0 AWG                                       |
| Conductor - ACSR Str Size        | 159 kcmil (12/7)                              |
| Conductor - ACSR Str Size Range  | 4/0 (6/1) Penquin AWG-159 (12/7) Guinea kcmil |
| Conductor - AL Str Size          | 4/0 AWG                                       |
| Conductor - AL Str Size Range    | 4/0 AWG                                       |

## Configuration

|                |        |
|----------------|--------|
| Connector Type | Sleeve |
|----------------|--------|

## Dimensions

|                              |            |
|------------------------------|------------|
| Package Length               | 0.000 in   |
| Package Width                | 0.000 in   |
| Package Weight               | 0.000 lb.  |
| Dimension - L Length Overall | 300 mm     |
| Package Height               | 0.000 in   |
| Dimension - Length Overall   | 11.82 inch |

## General

|                           |                |
|---------------------------|----------------|
| Die Index                 | 249            |
| Prefilled Oxide Inhibitor | Y              |
| Sub Brand                 | REPAIR SLEEVE  |
| Plated                    | N              |
| Type                      | YCU-R          |
| UPC 12 Digit              | 781810015261   |
| UPC 14 Digit GTIN         | 00781810015261 |
| Material                  | Aluminum       |
| Plating Type              | Unplated       |
| UPC                       | 781810015261   |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 25  |
| Carton Quantity       | 25  |
| Pallet Quantity       | 900 |

## Product Assets

[Catalog \[English\]](#)