



# YCS35R, Aluminum Sleeve, Staked Cable Stop

By Burndy  
Catalog # [YCS35R](#)

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), 8-7/8 IN L.

## Features

- HYSPLICE Sleeve designed to withstand jumper loop tensile and vibration stresses
- Made of aluminum with staked-in cable stop
- Pre-Filled with PENETROX Joint Compound and Capped

## Application


For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors

## Specifications

|                                              |                      |
|----------------------------------------------|----------------------|
| Buy American Compliant Certification - cULus | Contact Manufacturer |
| EU RoHS Indicator                            | No                   |
| Certification - UL Recognized                | Yes                  |
| Buy America(n) Qualified                     | No                   |
| Certification - ETL                          | Contact Manufacturer |
| Standards - RoHS Compliance Status           | No                   |
| Certification - CSA Approved                 | CM                   |
| UL Listed                                    | No                   |

## Conductor

|                                  |                                                                                                                                  |
|----------------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AAAC 5005 Size Range | 465.4 (19)                                                                                                                       |
| Conductor - AAAC 6201 Size       | 465.4 (19)                                                                                                                       |
| Conductor - AAAC 6201 Size Range | 465.4 (19)                                                                                                                       |
| Conductor - ACSR Str Size        | <ul style="list-style-type: none"><li>• 397.5 (18/1) Chickadee</li><li>• 397.5 (26/7) Ibis</li><li>• 397.5 (30/7) Lark</li></ul> |
| Conductor - ACSR Str Size Range  | 397.5 (18/1) Chickadee-397.5 (30/7) Lark                                                                                         |
| Conductor - AL Str Size          | 397.5                                                                                                                            |
| Conductor - AL Str Size Range    | 397.5                                                                                                                            |
| Conductor - AAAC 5005 Size       | 465.4 (19)                                                                                                                       |



## Configuration

|                |        |
|----------------|--------|
| Connector Type | Splice |
|----------------|--------|

## Dimensions

|                                 |            |
|---------------------------------|------------|
| Package Length                  | 0.000 in   |
| Package Width                   | 0.000 in   |
| Package Weight                  | 0.000 lb.  |
| Dimension - L Length Overall mm | 224 mm     |
| Package Height                  | 0.000 in   |
| Dimension - B Length fraction   | 4-22/71 in |
| Dimension - B Length inch       | 4.31 in    |
| Dimension - Length Overall inch | 8.8 in     |

## General

|                           |                |
|---------------------------|----------------|
| Die Index                 | 317            |
| Trade Name                | HYSPLICE™      |
| Prefilled Oxide Inhibitor | Y              |
| Sub Brand                 | HYSPLICE       |
| Plated                    | N              |
| Type                      | YCS-R          |
| UPC 12 Digit              | 781810821114   |
| UPC 14 Digit GTIN         | 00781810821114 |
| Material                  | Aluminum       |
| Plating Type              | Unplated       |
| UPC                       | 781810821114   |

## Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 25   |
| Carton Quantity       | 25   |
| Pallet Quantity       | 3600 |

## Product Assets

[Catalog \[English\]](#)