




YG14B2TC2C6C Compression Bus Bar Connector

By Burndy

Catalog # [YG14B2TC2C6C](#)

Copper Compression Bus Bar Connector, #6 Str/Sol and/or #2 Str/Sol to 1/4" Copper Busbar



Features

- Compression Busbar Connector
- Easier to use than exothermic connections
- Ideally suited for cellular tower applications
- High conductivity wrought copper connector for attaching ground conductor to ground bus with just one crimp when using BURNDY 750 Series of compression installation tools and U1105 die set (tool and die sold separately)
- Exclusive design allows for attachment of #2 AWG Sol/Str and/or #6Sol/Str copper conductor to 1/4" thick copper busbar
- Suitable for use on 1 or 2 conductors for power, grounding and bonding applications
- UL Listed to both UL486 and UL467 (Suitable for Direct Burial) ensures this connector meets the rigors of either application
- Prefilled with PENETROX E oxide inhibitor compound and strip sealed

Application

For Direct Burial And Cellular Tower Applications And Is Easier To Use Than Exothermic Connections

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	• UL467 • UL 486A • CSA C22.2 No 65
Certification - ETL	No
Standards - Industry Standards Met	• UL467 • UL 486A • CSA C22.2 No 65
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	6 AWG
Conductor - Copper Str Size B	2 AWG
Conductor - Copper Str Size A Range	6 AWG

Conductor - Copper Solid Size A	6 AWG
Conductor - Copper Solid Size B	2 AWG
Conductor - Copper Solid Size A Range	6 AWG
Conductor - Copper Solid Size B Range	6 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size • Bar-Size
Conductor - Copper Str Size B Range	2 AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Connector Type	Tap

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	64/79 in
Dimension - B Length inch	0.81 in
Dimension - Bus Bar Size Tap Side inch	1/4" Thick Busbar

General

Product Family	Grounding and Bonding Connectors>"Hyground" Compression Grounding Connectors>Wire to Bar HYGROUND®
Trade Name	Y
Prefilled Oxide Inhibitor	No
Plated	No
Sub Brand	HYGROUND
Product Type	Compression
UPC	781810199206
Type	YG-B
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810199206
UPC 14 Digit GTIN	00781810199206

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4640
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)



A Hubbell brand