



YGA262N Comp Ground Lug, 2/0 AWG Cu, 2-Hole NEMA Pad

By Burndy
Catalog # [YGA262N](#)

HYGROUND® Grounding Irreversible Compression Terminals



Features

- Irreversible Compression Grounding Lug
- Inspection port to ensure proper cable insertion
- UL 467 Listed, acceptable for direct burial in earth or concrete
- Prefilled with PENETROX Oxide Inhibiting Compound and strip sealed
- 2 Stud Holes, 1/2" with 1-3/4" Spacing
- Die Index: 13

Application

For Grounding Applications And Direct Burial In Earth Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	2/0 Str.
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	2/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.81 in
Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	126 mm
Dimension - Outside Diameter inch	0.56 in
Dimension - Width fraction	1/2 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - B Length fraction	1-4/9 in
Dimension - Width inch	0.53 in
Dimension - B Length inch	1.45 in
Dimension - N inch	0.62 in
Dimension - Bolt Size inch	0.50 in
Dimension - Length Overall inch	4.97 in

General

Product Family	Grounding and Bonding Connectors>"Hyground" Compression Grounding Connectors>Terminals
Trade Name	HYLUG™
Die Index	13
Plated	No
Color Code	Black
Sub Brand	HYLUG
Product Type	Compression
UPC	781810220313
Type	Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220313
UPC 14 Digit GTIN	00781810220313

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9600
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)

