



YGA342N Comp Ground Lug, 500 kcmil Cu, 2-Hole NEMA Pad

By Burndy

Catalog # [YGA342N](#)

HYLUG™ Copper Compression Terminal for Grounding; 2-Hole



Features

- Irreversible compression ground terminal specifically designed for grounding applications
- Each connector has an inspection probe hole to ensure proper cable insertion
- UL467 Listed
- Acceptable for Direct Burial in earth or concrete
- UL486A Listed
- Prefilled with PENETROX™ compound and strip sealed

Application

For Direct Burial In Earth Or Concrete, Grounding Applications

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	500 kcmil
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	500 kcmil

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.52 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	154 mm
Dimension - Outside Diameter inch	1.06 in
Dimension - Width fraction	2/5 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	2-5/16
Dimension - Stud Size inch	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - B Length fraction	2-1/5 in
Dimension - Width inch	0.41 in
Dimension - B Length inch	2.20 in
Dimension - N inch	0.62 in
Dimension - Bolt Size inch	0.50 in
Dimension - Length Overall inch	6.08 in

General

Trade Name	HYLUG™
Die Index	• 20 • 299
Plated	N
Color Code	Brown
Sub Brand	HYLUG
UPC	781810220344
Type	Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220344
UPC 14 Digit GTIN	00781810220344

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2784
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)



A Hubbell brand