




YGF344N Grounding Plate, 250-500 kcmil Cu, 4-Hole NEMA Pad

By Burndy

Catalog # [YGF344N](#)

Compression Grounding Plate; Copper; 4-Hole



Features

- Compression Grounding Plate designed for the rigors of concrete construction
- Made of high strength, high-conductivity cast copper alloy body
- Plate comes with a tapped hole on the underside for ease of positioning prior to pouring concrete
- UL467 Listed, Acceptable for direct burial in earth or concrete
- Prefilled with oxide inhibiting compound and strip sealed

Application

Used to position the grounding plate on a threaded rod prior to placement of the concrete.

Specifications

Certification - UL Recognized	No
Buy American Compliant	Yes
Certification - cULus	No
Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2026)
Industry Standard(s)	NEMA Size Holes
Certification - ETL	No
Standards - Industry Standards Met	• UL467 • IEEE 837
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	250 kcmil-500 kcmil

Configuration

Physical Attribute - Number of Tapped Holes	4
Physical Attribute - Number of Crimps Required	2



A Hubbell brand

Dimensions

Dimension - Pad Width inch	3.75 in
Package Height	0.000 in
Dimension - Height mm	117.3 mm
Dimension - Height inch	4.62 in
Dimension - Height fraction	4-31/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	150 mm
Dimension - Thread Size	3/8 -16
Physical Attribute - Tongue Angle	Straight
Dimension - D inch	3.75 in
Dimension - Length Overall inch	5.90 in

General

Product Family	Grounding and Bonding Connectors>"Hyground" Compression Grounding Connectors>Ground Plate Connectors
Trade Name	HYGROUND®
Die Index	1011
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	GROUNDING PLATE
Product Type	Compression
UPC	781810220528
Type	YGF
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220528
UPC 14 Digit GTIN	00781810220528

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	2

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)