



# YGHA26NTN Comp Ground Lug, 2/0 AWG Cu, 1-Hole, 1/2", Tinned

By Burndy  
Catalog # [YGHA26NTN](#)



HYLUG™ Copper Compression Terminal for Grounding; Heavy  
Duty; 1-Hole

### Features

- Irreversible compression ground terminal specifically designed for grounding applications
- Each connector has an inspection probe hole to ensure proper cable insertion
- UL467 Listed
- Acceptable for Direct Burial in earth or concrete
- UL486A Listed
- Prefilled with PENETROX™ compound and strip sealed

### Specifications

|                                         |                                                                                                  |
|-----------------------------------------|--------------------------------------------------------------------------------------------------|
| Certification - ETL                     | No                                                                                               |
| Certification - UL Recognized           | No                                                                                               |
| Standards - Industry Standards Met      | <ul style="list-style-type: none"><li>• UL467</li><li>• UL468A-468B</li><li>• IEEE 837</li></ul> |
| Standards - RoHS Compliance Status      | CM                                                                                               |
| Certification - cULus                   | No                                                                                               |
| Certification - UL Listed Direct Burial | Yes                                                                                              |
| UL Listed                               | No                                                                                               |
| Certification - CSA Approved            | No                                                                                               |

### Conductor

|                                   |                                                                                           |
|-----------------------------------|-------------------------------------------------------------------------------------------|
| Conductor Type                    | <ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Solid-Size</li></ul> |
| Conductor - Copper Str Size Range | 2/0 AWG                                                                                   |
| Conductor - Copper Str Size       | 2/0 AWG                                                                                   |

### Configuration

|                                                |          |
|------------------------------------------------|----------|
| Physical Attribute - Number of Crimps Required | 1        |
| Connector Type                                 | Terminal |

### Dimensions

|                            |         |
|----------------------------|---------|
| Dimension - Pad Width inch | 0.97 in |
|----------------------------|---------|

|                                   |           |
|-----------------------------------|-----------|
| Package Height                    | 0.000 in  |
| Physical Attribute - Tongue Angle | Straight  |
| Dimension - B Length fraction     | 39/47 in  |
| Package Weight                    | 0.000 lb. |
| Package Length                    | 0.000 in  |
| Package Width                     | 0.000 in  |
| Dimension - Z inch                | 0.64 in   |
| Dimension - L Length Overall mm   | 67 mm     |
| Dimension - B Length inch         | 0.83 in   |
| Dimension - Outside Diameter inch | 0.71 in   |
| Dimension - D inch                | 1.27 in   |
| Dimension - N inch                | 0.63 in   |
| Dimension - Hole Size mm          | 14 mm     |
| Dimension - Hole Size inch        | 0.56 in   |
| Dimension - Length Overall inch   | 2.63 in   |

### General

|                   |                      |
|-------------------|----------------------|
| Plated            | Y                    |
| Trade Name        | HYLUG™               |
| Die Index         | 15                   |
| UPC               | 781810346631         |
| Type              | Terminals            |
| Material          | Copper               |
| Plating Type      | Tin - Electro Plated |
| UPC 12 Digit      | 781810346631         |
| UPC 14 Digit GTIN | 00781810346631       |

### Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 1     |
| Pallet Quantity       | 11600 |
| Carton Quantity       | 25    |

### Product Assets

[Catalog \[English\]](#)