



**YGHC26C2 C-Tap, Run: 1-2/0 Str, 3/8" Rod,
Tap: 6 Sol-2 Str**

By Burndy

Catalog # [YGHC26C2](#)

HYGROUND® Compression Grounding C TAP; 1-2/0 AWG Str, 3/8" Rod
Run, #6 AWG Sol-#2 AWG Str Tap



Features

- Irreversible compression ground tap figure C connector
- C-shaped opening permits placing two continuous parallel cables into conductor groove
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Application

For Direct Burial Cables

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Industry Standard(s)	Direct Burial
Certification - ETL	No
Standards - Industry Standards Met	• UL467 • IEEE 837 • IEEE 837 2014 Qualified • UL468A-468B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Rod Run Range	3/8 in
Conductor - Rod Run	3/8 in
Conductor - Copper Str Run Range	1 AWG-2/0 AWG
Conductor - Copper Str Run	• 1 AWG • 1/0 • 2/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-2 AWG
Conductor - Copper Solid Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor - Copper Str Tap	• 6 AWG • 5 AWG

- 4 AWG
- 3 AWG
- 2 AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	35.8 mm
Dimension - Height inch	1.41 in
Dimension - Height fraction	1-25/61 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	19 mm
Dimension - B Length inch	0.75 in
Dimension - Length Overall inch	0.75 in

General

Product Family	Grounding and Bonding Connectors>"Hyground" Compression Grounding Connectors>C-Taps
Trade Name	HYTAP™
Die Index	O
Plated	No
Sub Brand	HYGROUND, HYTAP
Product Type	Compression
UPC	781810221020
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810221020
UPC 14 Digit GTIN	00781810221020

Logistics

Minimum Pack Quantity	1
Pallet Quantity	14800
Carton Quantity	75

Product Assets

[Catalog \[English\]](#)



A Hubbell brand