



YHD400, Line Tap Connector, AL-CU, AL-AL

By Burndy
Catalog # [YHD400](#)

Compression Line Tap for Copper, AL or ACSR and Compact Conductors



Features

- Wide range, Universal and Reversible Figure H Shapped aluminum compression connector
- Bendable tabs secure both run and tap conductors freeing the installers hands to work with the installation tool
- Massive aluminum design minimizes corrosion due to galvanic corrosion
- Pre-filled with PENETROX Joint Compound and individually packaged
- Conductor ranges and tooling is clearly printed on connector and package

Application

For Copper, Aluminum Or ACSR And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	3/0 AWG-266.8 kcmil
Conductor - ACSR Cmpt Run	• 3/0 AWG • 4/0 AWG • 266.8 kcmil
Conductor - AL Str Run Range	3/0 AWG-4/0 AWG
Conductor - AL Str Run	• 3/0 AWG • 4/0 AWG
Conductor - AL Str Tap Range	4/0 AWG
Conductor - AL Str Tap	4/0 AWG
Conductor - ACSR Cmpt Tap Range	3/0 AWG-266.8 kcmil
Conductor - ACSR Cmpt Tap	• 3/0 AWG • 4/0 AWG • 266.8 kcmil
Conductor - ACSR Str Run Range	3/0 (6/1) Pigeon AWG-4/0 (6/1) Penquin AWG

Conductor - ACSR Str Run	• 3/0 (6/1) Pigeon AWG • 4/0 (6/1) Penquin AWG
Conductor - ACSR Str Tap Range	3/0 (6/1) Pigeon AWG-4/0 (6/1) Penquin AWG
Conductor - ACSR Str Tap	• 3/0 (6/1) Pigeon AWG • 4/0 (6/1) Penquin AWG
Conductor - Copper Str Run Range	3/0 AWG-4/0 AWG
Conductor - Copper Str Run	• 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Run Range	250 - 300
Conductor - Copper Solid Run	250 - 300
Conductor - Copper Solid Tap Range	250-300
Conductor - Copper Solid Tap	• 250 • 300
Conductor - Copper Str Tap Range	4/0 AWG
Conductor - Copper Str Tap	4/0 AWG

Dimensions

Package Height	2.800 in
Dimension - Height mm	35.6 mm
Dimension - Height inch	1.40 in
Dimension - Height fraction	1-49/100 in
Package Weight	4.500 lb.
Package Length	13.400 in
Package Width	4.900 in
Dimension - L Length Overall mm	64 mm
Dimension - Width fraction	89/100 in
Dimension - Width mm	21 mm
Dimension - Width inch	0.84 in
Dimension - Length Overall inch	2.50 in

General

Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>H-Taps
Trade Name	HYCRIMP™
Die Index	D3
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	HYCRIMP
Product Type	Compression
UPC	781810139356
Type	YHD
Material	Aluminum

Plating Type	Unplated	Pallet Quantity	3200
UPC 14 Digit GTIN	00781810139356	Carton Quantity	200

Logistics

Minimum Pack Quantity25



A Hubbell brand

Product Assets

[Catalog \[English\]](#)