



YHD6, Line Tap Connector, AL-CU, AL-AL

By Burndy
Catalog # [YHD6](#)

Compression Line Tap Connector for Aluminum to Copper and Aluminum to Aluminum applications, 1.42 H, 2.25 L, .83 W



Features

- LOKTAP™ compression connectors are high quality, range-taking devices accommodating many combinations of conductor
- LOKTAP™ connectors feature a C groove on both sides of the connector for use in street lighting applications

Application

For Accommodate Combinations Of Aluminum To Copper, And Aluminum To Aluminum Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	3/0 AWG-266.8 kcmil
Conductor - ACSR Cmpt Run	• 3/0 AWG • 4/0 AWG • 266.8 kcmil
Conductor - AL Str Run Range	3/0 AWG-4/0 AWG
Conductor - AL Str Run	• 3/0 AWG • 4/0 AWG
Conductor - AL Str Tap Range	1 AWG-2/0 AWG
Conductor - AL Str Tap	• 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - ACSR Cmpt Tap Range	1/0 AWG-2/0 AWG
Conductor - ACSR Cmpt Tap	• 1/0 AWG • 2/0 AWG
Conductor - ACSR Str Run Range	3/0 (6/1) Pigeon AWG-4/0 (6/1) Penquin AWG
Conductor - ACSR Str Run	• 3/0 (6/1) Pigeon AWG • 4/0 (6/1) Penquin AWG
Conductor - ACSR Str Tap Range	1 (6/1) Robin AWG-2/0 (6/1) Quail AWG
Conductor - ACSR Str Tap	• 1 (6/1) Robin AWG • 1/0 (6/1) Raven AWG

Conductor - Copper Str Run Range	3/0 AWG-4/0 AWG
Conductor - Copper Str Run	• 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Run Range	250 KCMIL-300 KCMIL
Conductor - Copper Solid Run	• 250 KCMIL • 300 KCMIL
Conductor - Copper Solid Tap Range	2/0 AWG-3/0 AWG
Conductor - Copper Solid Tap	• 2/0 AWG • 3/0 AWG
Conductor - Copper Str Tap Range	1 AWG-2/0 AWG
Conductor - Copper Str Tap	• 1 AWG • 1/0 • 2/0 AWG

Dimensions

Package Height	2.800 in
Dimension - Height mm	36.1 mm
Dimension - Height inch	1.42 in
Dimension - Height fraction	1-21/50 in
Package Weight	4.020 lb.
Package Length	13.300 in
Package Width	4.750 in
Dimension - L Length Overall mm	57 mm
Dimension - Width fraction	83/100 in
Dimension - Width mm	21 mm
Dimension - Width inch	0.83 in
Dimension - Length Overall inch	2.25 in

General

Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>H-Taps
Trade Name	LOKTAP™
Die Index	D3
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	LOKTAP
Product Type	Compression
UPC	781810139134
Type	YHD
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810139134

Logistics

Minimum Pack Quantity	25
Pallet Quantity	3200

Carton Quantity200

Product Assets

[Catalog \[English\]](#)



A Hubbell brand