



YGA6C2N Comp Ground Lug, #6 AWG Cu, 2-Hole NEMA Pad

By Burndy
Catalog # [YGA6C2N](#)

HYLUG™ Copper Compression Terminal for Grounding; 2-Hole



Features

- Irreversible compression ground terminal specifically designed for grounding applications
- Each connector has an inspection probe hole to ensure proper cable insertion
- UL467 Listed
- Acceptable for Direct Burial in earth or concrete
- UL486A Listed
- Prefilled with PENETROX™ compound and strip sealed

Application

HYLUG ground terminal specially designed for grounding applications

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	6 Sol./6 Str.
Conductor - Copper Solid Size	6 AWG
Conductor - Copper Solid Size Range	6 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	6 Sol / 6 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.83 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	112 mm
Dimension - Outside Diameter inch	0.29 in
Dimension - Width fraction	2/5 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - B Length fraction	1 in
Dimension - Width inch	0.41 in
Dimension - B Length inch	1.09 in
Dimension - N inch	0.62 in
Dimension - Bolt Size inch	0.50 in
Dimension - Length Overall inch	4.40 in

General

Trade Name	HYLUG™
Die Index	• 7 • 374
Plated	N
Color Code	Blue
Sub Brand	HYLUG
UPC	781810091739
Type	YGA-2N
Construction Material - Main Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810091739
UPC 14 Digit GTIN	00781810091739

Logistics

Minimum Pack Quantity	1
Pallet Quantity	24000
Carton Quantity	100



A Hubbell brand