




YKA34CA2N, Cast Aluminum Disconnectable Terminal

By Burndy
Catalog # [YKA34CA2N](#)



Cast Al Disconnectable Terminal, 397.5 (26-7, 30-7) 477 (18-1) kcmil ACSR, 500 (19, 37) kcmil Cu, 477 (19, 37) 500 (37, 61) kcmil Al, Flat Sided Brll

Features

- Cast Aluminum Disconnectable Terminal

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - AAAC 5005 Size Range	465.4 (19) kcmil-559.5 (19) kcmil
Conductor - AAAC 6201 Size	• 465.4 (19) kcmil • 559.5 (19) kcmil
Conductor - AAAC 6201 Size Range	465.4 (19) kcmil-559.5 (19) kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - ACSR Str Size	• 397.5 (26/7) lbis kcmil • 397.5 (30/7) Larkspur kcmil • 477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Size Range	397.5 (26/7) lbis kcmil-477.0 (18/1) Pelican kcmil
Conductor - AL Str Size	• 477 kcmil • 500 kcmil
Conductor - AL Str Size Range	477 kcmil-500 kcmil
Conductor - Copper Str Size Range	500 kcmil
Conductor - AAAC 5005 Size	• 465.4 (19) kcmil • 559.5 (19) kcmil

Configuration

Physical Attribute - Pad Configuration	Straight
Connector Type	Terminal

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Pad Width inch	1.90 in
Package Height	0.000 in
Dimension - Thread Size	1/2
Dimension - B Length fraction	1-3/4 in
Dimension - Bolt Size fraction	1/2

General

Die Index	• 352 • 579
Prefilled Oxide Inhibitor	Y
Plated	N
UPC 12 Digit	781810017036
UPC 14 Digit GTIN	00781810017036
Material	Aluminum
Plating Type	Unplated
UPC	781810017036

Logistics

Minimum Pack Quantity	3
Carton Quantity	8
Pallet Quantity	840

Product Assets

[Catalog \[English\]](#)