



YGL2C2 Cross Grid, Cu Wire Run to Cu Wire Tap

By Burndy
Catalog # YGL2C2



Copper Compression Cross Grid Connector, 6 AWG (Sol.) - 2 AWG (Str.), 6 AWG (Sol.) - 2 AWG (Str.)

Features

- Irreversible compression ground grid cross connector allows adjustment of the compression elements prior to installation
- UL467 Listed
- Acceptable for Direct Burial in earth and concrete
- Prefilled with PENETROX™ compound and strip sealed

Application

For Direct Burial In Earth And Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	• UL467 • IEEE 837 • IEEE 837 2014 Qualified
Certification - ETL	No
Standards - Industry Standards Met	• UL467 • IEEE 837 • IEEE 837 2014 Qualified
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size A	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Str Size B	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Str Size A Range	6 AWG-2 AWG
Conductor - Copper Solid Size A	• 6 AWG • 5 AWG

Conductor - Copper Solid Size B	• 4 AWG • 3 AWG • 2 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Solid Size A Range	6 AWG-2 AWG
Conductor - Copper Solid Size B Range	6 AWG-2 AWG
Conductor Type	• CU C Solid-Size A • CU C Str-Size A • Rod-Size A • Rebar-Size A • CU C Solid-Size B • CU C Str-Size B
Conductor - Copper Str Size B Range	6 AWG-2 AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - Pad Width inch	1.09 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	64 mm
Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - D inch	0.31 in
Dimension - Length BB inch	0.75 in
Dimension - Length Overall inch	2.50 in

General

Product Family	Grounding and Bonding Connectors>"Hyground" Compression Grounding Connectors>Cross Grid Connections
Trade Name	HYGRID™
Oxide Inhibitor Type	Penetrox E
Prefilled Oxide Inhibitor	Y

Plated	No
Sub Brand	HYGRID
Product Type	Compression
UPC	781810220009
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220009
UPC 14 Digit GTIN	00781810220009

Logistics

Minimum Pack Quantity	1
Pallet Quantity	6000
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)



A Hubbell brand