



YHD5, Line Tap Connector, AL-CU, AL-AL

By Burndy
Catalog # [YHD5](#)

Compression Line Tap Connector for Aluminum to Copper and Aluminum to Aluminum applications, 1.47 H, 1.88 L, .87 W



Features

- LOKTAP™ compression connectors are high quality, range-taking devices accommodating many combinations of conductor
- LOKTAP™ connectors feature a C groove on both sides of the connector for use in street lighting applications

Application

For Accommodate Combinations Of Aluminum To Copper, And Aluminum To Aluminum Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	4/0 AWG-266
Conductor - ACSR Cmpt Run	• 4/0 AWG • 266
Conductor - AL Str Run Range	4/0 AWG
Conductor - AL Str Run	4/0 AWG
Conductor - AL Str Tap Range	6 AWG-2 AWG
Conductor - AL Str Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - ACSR Cmpt Tap Range	6 AWG-1 AWG
Conductor - ACSR Cmpt Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor - ACSR Str Run Range	3/0 (6/1) Pigeon AWG-4/0 (6/1) Penquin AWG
Conductor - ACSR Str Run	• 3/0 (6/1) Pigeon AWG • 4/0 (6/1) Penquin AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG

Conductor - ACSR Str Tap	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - Copper Str Run Range	4/0 AWG
Conductor - Copper Str Run	4/0 AWG
Conductor - Copper Solid Run Range	250 kmcil-300 kcmil
Conductor - Copper Solid Run	• 250 kmcil • 300 kcmil
Conductor - Copper Solid Tap Range	#6-1/0
Conductor - Copper Solid Tap	• #6 • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1/0
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

Dimensions

Package Height	2.750 in
Dimension - Height mm	37.3 mm
Dimension - Height inch	1.47 in
Dimension - Height fraction	1-47/100 in
Package Weight	3.680 lb.
Package Length	11.100 in
Package Width	4.800 in
Dimension - L Length Overall mm	48 mm
Dimension - Width fraction	87/100 in
Dimension - Width mm	22 mm
Dimension - Width inch	0.87 in
Dimension - Length Overall inch	1.88 in

General

Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>H-Taps
----------------	---

Trade Name	LOKTAP™	UPC 14 Digit GTIN	00781810139080
Die Index	D3		
Prefilled Oxide Inhibitor	Y	Logistics	
Plated	No	Minimum Pack Quantity	25
Sub Brand	LOKTAP	Pallet Quantity	4000
Product Type	Compression	Carton Quantity	250
UPC	781810139080		
Type	YHD	Product Assets	
Material	Aluminum	Catalog [English]	
Plating Type	Unplated		

