

YHN550, Line Tap for CU, AL, ACSR, Compact

By Burndy
Catalog # [YHN550](#)

Compression Line Tap for Copper, AL or ACSR and Compact Conductors, groove A(Run) ACSR:266.8 (18/1) - 477.0 (18/1)

Features

- Wide range, universal and reversible Figure H -Shaped aluminum connector
- Conductors are separated by the shape of the connector
- Bendable tabs secure both run and tap conductors freeing the installer's hands to work with the installation tool
- Massive aluminum design minimizes corrosion due to galvanic corrosion
- Pre-filled with PENETROX Joint Compound and individually packaged

Application

For Copper, Aluminum Or ACSR And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	300 - 556.5
Conductor - ACSR Cmpt Run	300 - 556.5
Conductor - AL Str Run Range	250 - 500
Conductor - AL Str Run	250 - 500
Conductor - AL Str Tap Range	2/0 - 4/0
Conductor - AL Str Tap	2/0 - 4/0
Conductor - ACSR Cmpt Tap Range	2/0 AWG - 266.8
Conductor - ACSR Cmpt Tap	2/0 AWG - 266.8
Conductor - ACSR Str Run Range	266.8 (18/1) - 477 (18/1)
Conductor - ACSR Str Run	266.8 (18/1) - 477 (18/1)
Conductor - ACSR Str Tap Range	2/0 (6/1) - 4/0 (6/1)
Conductor - ACSR Str Tap	2/0 (6/1) - 4/0 (6/1)
Conductor - Copper Solid Tap Range	3/0 - 300



Conductor - Copper Solid Tap	3/0 - 300
Conductor - Copper Str Tap Range	2/0 - 4/0
Conductor - Copper Str Tap	2/0 - 4/0

Dimensions

Package Height	0.000 in
Dimension - Height mm	49.8 mm
Dimension - Height inch	1.96 in
Dimension - Height fraction	1-24/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	51 mm
Dimension - Width fraction	1-7/25 in
Dimension - Width mm	33 mm
Dimension - Width inch	1.28 in
Dimension - Length Overall inch	2.00 in

General

Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>H-Taps
Trade Name	HYCRIMP™
Die Index	N
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	HYCRIMP
Product Type	Compression
UPC	781810139554
Type	YHN
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810139554

Logistics

Minimum Pack Quantity	50
Pallet Quantity	2400
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)