


YP28U26, Figure 3-shaped Aluminum Connector with adjustable spacer

By Burndy
Catalog # [YP28U26](#)



Wide range, universal and reversible, Figure 3 shaped aluminum connector with adjustable overhanging spacer that separates conductors, Conductor Groove A ACSR: 3/0, 4/0.

Features

- Wide range universal and reversible, Figure 3-shaped aluminum connector features adjustable overhanging spacer that separates conductors
- Spacer holds run or tap in place, permitting lineman to either approach the line ready to crimp or to assemble connector and tap on run and then crimp
- Massive aluminum design minimizes conductor corrosion due to galvanic action
- Pre-filled with PENETROX joint compound and stripsealed

Application

For Copper, Aluminum Or ACSR Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size A	• 3/0 AWG • 4/0 AWG
Conductor - AL Str Size B	• 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - AL Str Size A Range	3/0 AWG-4/0 AWG
Conductor - AL Str Size B Range	1 AWG-2/0 AWG
Conductor - ACSR Str Size A	• 3/0 (6/1) Pigeon AWG • 4/0 (6/1) Penguin AWG
Conductor - ACSR Str Size B	• 1 (6/1) Robin AWG • 1/0 (6/1) Raven AWG • 2/0 (6/1) Quail AWG
Conductor - ACSR Str Size A Range	3/0 (6/1) Pigeon AWG-4/0 (6/1) Penguin AWG
Conductor - ACSR Str Size B Range	1 (6/1) Robin AWG-2/0 (6/1) Quail AWG

Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size B	• 1/0 • 2/0 AWG
Conductor - Copper Solid Size B	• 2/0 AWG • 3/0 AWG
Conductor - Copper Str Size B Range	1/0 -2/0 AWG

Dimensions

Package Height	0.000 in
Dimension - Height inch	1.70 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Width inch	0.97 in
Dimension - Length Overall inch	3.47 in

General

Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>C-Taps
Trade Name	CABELOK™ CRIMPIT™
Die Index	D3
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	CABELOK CRIMPIT
Product Type	Compression
UPC	781810135532
Type	YP-U
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810135532
UPC 14 Digit GTIN	00781810135532

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2400
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)