

YPC2A8U, Figure 6-shaped Connector

By Burndy
Catalog # [YPC2A8U](#)

Compact compression connector designed to tap small lighting wires from secondaries. Figure 6-shape separates run and tap, and minimizes galvanic corrosion.

Features

- Compact compression connector designed to tap small lighting wires from secondaries
- Figure 6-shape separates run and tap, minimizing galvanic corrosion
- Connector can be gripped in tool and slipped over line for easier installation
- Pre-filled with PENETROX joint compound and stripsealed

Application

For Combinations Of Copper, Aluminum, ACSR, Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	6 AWG-2 AWG
Conductor - AL Str Run	• 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - AL Str Tap	8 AWG
Conductor - ACSR Str Run Range	6 (6/1) Turkey AWG-4 (7/1) Swanate AWG
Conductor - ACSR Str Run	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG
Conductor - Copper Str Run Range	6 AWG-2 AWG
Conductor - Copper Str Run	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Solid Run Range	4 AWG-2 AWG



Conductor - Copper Solid Run	• 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Solid Tap	14 AWG
Conductor Type	• AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap
Conductor - Copper Str Tap Range	14 AWG-8 AWG
Conductor - Copper Str Tap	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	25 mm
Dimension - Height inch	0.97 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	18 mm
Dimension - Width inch	0.56 in
Dimension - Length Overall inch	0.69 in

General

Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>YPC Figure 6
Trade Name	CRIMPIT™
Die Index	BG or 5/8
Plated	No
Sub Brand	CRIMPIT
Product Type	Compression
UPC	781810135686
Type	YPC-A-U
Plating Type	Unplated
UPC 12 Digit	781810135686
UPC 14 Digit GTIN	00781810135686

Logistics

Minimum Pack Quantity	1
-----------------------	---

Pallet Quantity 6800
Carton Quantity 100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand