



YPC33R28R, Figure 6-shaped Connector

By Burndy
Catalog # [YPC33R28R](#)

Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run, Al and Cu:250 (37) - 477 (37)



Features

- Extra wide range universal compression connector
- Figure 6-shape separates run and tap wires minimizes galvanic corrosion of conductors
- Connector can be gripped in tool and slipped over line for easy installation
- Pre-filled with PENETROX joint compound and stripsealed

Application

For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 And Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	250 kcmil-477 kcmil
Conductor - AL Str Run	• 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil
Conductor - AL Str Tap Range	2/0 AWG-4/0 AWG
Conductor - AL Str Tap	• 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - ACSR Str Run Range	266.8 kcmil-397.5 kcmil
Conductor - ACSR Str Tap Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Run Range	250 kcmil-477 kcmil
Conductor - Copper Str Run	• 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil

Conductor Type

- 350 kcmil
- 397 kcmil
- 400 kcmil
- 450 kcmil
- 477 kcmil
- AL C Str-Run
- CU C Str-Run
- CU C Solid-Run
- ACSR C Str-Run
- AL C Str-Tap
- CU C Str-Tap
- CU C Solid-Tap
- ACSR C Str-Tap

Conductor - Copper Str Tap Range

2/0 AWG-4/0 AWG

Conductor - Copper Str Tap

- 2/0 AWG
- 3/0 AWG
- 4/0 AWG

Dimensions

Package Height	0.000 in
Dimension - Height inch	2.28 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	98 mm
Dimension - Width inch	1.16 in
Dimension - Length Overall inch	3.88 in

General

Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>YPC Figure 6
Trade Name	CRIMPIT™
Die Index	N
Plated	No
Sub Brand	CRIMPIT
Product Type	Compression
UPC	781810138007
Type	YPC-U
Construction Material - Main	Aluminum
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810138007
UPC 14 Digit GTIN	00781810138007

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1200
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)



A Hubbell brand