



YPC26R8U, Compression Figure-6 Shape Connector, Separates Run and Tap

By Burndy
Catalog # [YPC26R8U](#)

Compact compression connector designed to tap small lighting wires from secondaries. Figure 6-shape separates run and tap, and minimizes galvanic corrosion.

Features

- Compact compression connector designed to tap small lighting wires from secondaries
- Figure 6-shape separates run and tap, minimizing galvanic corrosion
- Connector can be gripped in tool and slipped over line for easier installation
- Pre-filled with PENETROX joint compound and stripsealed

Application

For Combinations Of Copper, Aluminum, ACSR, Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	1 AWG-3/0 AWG
Conductor - AL Str Run	• 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG
Conductor - AL Str Tap	8 AWG
Conductor - ACSR Str Run Range	2 (6/1) Sparrow AWG-3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Run	• 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG • 1 (6/1) Robin AWG • 1/0 (6/1) Raven AWG • 2/0 (6/1) Quail AWG • 3/0 (6/1) Pigeon AWG
Conductor - Copper Str Run Range	1 AWG-3/0 AWG
Conductor - Copper Str Run	• 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG



Conductor - Copper Solid Run	18 AWG
Conductor - Copper Solid Tap	14 AWG
Conductor Type	• AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap
Conductor - Copper Str Tap Range	14 AWG-8 AWG
Conductor - Copper Str Tap	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	33 mm
Dimension - Height inch	1.30 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	19 mm
Dimension - Width inch	0.73 in
Dimension - Length Overall inch	0.75 in

General

Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>YPC Figure 6
Trade Name	CRIMPIT™
Die Index	O
Plated	No
Sub Brand	CRIMPIT
Product Type	Compression
UPC	781810137376
Type	YPC-R-U
Plating Type	Unplated
UPC 12 Digit	781810137376
UPC 14 Digit GTIN	00781810137376

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7200

Carton Quantity

100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-YPC26R8U-SPEC-EN | REV 7/2026