



YPC33R33R, Figure 6-shaped Connector

By Burndy
Catalog # YPC33R33R

Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run ACSR, 5005:266.8 (18-1) - 397.5 (18-1)

Features

- Extra wide range universal compression connector
- Figure 6-shape separates run and tap wires minimizes galvanic corrosion of conductors
- Connector can be gripped in tool and slipped over line for easy installation
- Pre-filled with PENETROX joint compound and stripsealed

Application

For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 And Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	250 kcmil-400 kcmil
Conductor - AL Str Run	• 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil
Conductor - AL Str Tap Range	250 kcmil-400 kcmil
Conductor - AL Str Tap	• 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil
Conductor - ACSR Str Run Range	266.8 kcmil-397.5 kcmil
Conductor - ACSR Str Tap Range	266.8 kcmil-397.5 kcmil
Conductor - Copper Str Run Range	250 kcmil-400 kcmil
Conductor - Copper Str Run	• 250 kcmil • 300 kcmil • 350 kcmil



Conductor Type	• 400 kcmil • AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap • ACSR C Str-Tap
Conductor - Copper Str Tap Range	250 kcmil-400 kcmil
Conductor - Copper Str Tap	• 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height inch	2.28 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	98 mm
Dimension - Width inch	1.23 in
Dimension - Length Overall inch	3.88 in

General

Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>YPC Figure 6
Trade Name	CRIMPIT™
Die Index	N
Plated	No
Sub Brand	CRIMPIT
Product Type	Compression
UPC	781810138205
Type	YPC-U
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810138205
UPC 14 Digit GTIN	00781810138205

Logistics

Minimum Pack Quantity	25
Pallet Quantity	1100
Carton Quantity	25



A Hubbell brand