


YSH2929 Compression H-Tap Connector

By Burndy
Catalog # [YSH2929](#)

Copper Split Compression Wye Tap Connector, 250- # 2 (Run & Tap),
Provides maximum design and installation flexibility.



Features

- Accommodates a wide range of Run/Tap Copper cable combinations including both flexible and code combinations allowing maximum flexibility
- Tap grooves function independently from each other, use of one tap is required, balance may be used or left empty

Application

For High Voltage (15 KV) Power Cables With Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Run Range	2 AWG-250 kcmil
Conductor - Copper Flex G Run	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - Copper Flex H Run Range	2 AWG-250 kcmil
Conductor - Copper Flex H Run	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - Copper Str Run Range	2 AWG-250 kcmil
Conductor - Copper Flex G Tap Range	2 AWG-250 kcmil
Conductor - Copper Str Run	• 2 AWG • 1 AWG

Conductor - Copper Flex G Tap	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - Copper Flex H Tap Range	2 AWG-250 kcmil
Conductor - Copper Flex H Tap	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - Copper Str Tap Range	2 AWG-250 kcmil
Conductor - Copper Str Tap	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	H-Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	47 mm
Dimension - Height inch	1.85 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Strip Length inch	1 1/2
Dimension - Width mm	23 mm
Dimension - Width inch	0.90 in
Dimension - Length Overall inch	3.00 in

General

Trade Name	CRIMPIT™
Die Index	654
Plated	Yes
Color Code	Purple
Sub Brand	CRIMPIT
Product Type	Compression
UPC	781810036969
Type	Taps
Material	Copper
Plating Type	Tin

UPC 12 Digit	781810036969
UPC 14 Digit GTIN	00781810036969

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2880
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)



A Hubbell brand