



YSU2W4W, Heavy-Walled Aluminum Tube with Solid Barrier

By Burndy
Catalog # [YSU2W4W](#)



Heavy-walled AL tubing with solid barrier minimizes galvanic corrosion, Color Code:Orange (Side A), Blue (Color Code)

Features

- Heavy-walled aluminum tube with solid barrier minimizes galvanic corrosion of conductors
- Accommodates neutral strands of SE Service Entrance Conductors as well as others
- Installed with standard tooling, color-coded, and pre-filled with PENETROX Joint Compound and Stripsealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	3 AWG, 4 AWG
Conductor - Copper Str Size B	5 AWG, 6 AWG
Conductor - Copper Str Size A Range	3 AWG-4 AWG
Conductor - Copper Solid Size A	2 AWG
Conductor - Copper Solid Size B	4 AWG
Conductor - AL Str Size A	3 AWG, 4 AWG
Conductor - AL Str Size B	5 AWG, 6 AWG
Conductor - AL Str Size A Range	3 AWG- 4 AWG
Conductor - AL Str Size B Range	5 AWG-6 AWG
Conductor - ACSR Str Size A	• 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG
Conductor - ACSR Str Size B	6 (6/1) Turkey AWG
Conductor - ACSR Str Size A Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - Copper Str Size B Range	5 AWG-6 AWG

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	51 mm
Dimension - B Length inch	0.87 in
Dimension - Outside Diameter	0.65 in
Dimension - Length Overall	2 in

General

Plated	Y
Trade Name	LINKIT™
Die Index	• 243 • BG or 5/8
UPC	781810142080
Color Code - Side B	Blue
Color Code - Side A	Orange
Type	Service Entrance, Uninsulated, Center Stop
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810142080
UPC 14 Digit GTIN	00781810142080

Logistics

Minimum Pack Quantity	100
Pallet Quantity	29600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)