



YSU4W6W, Heavy-Walled Aluminum Tube with Solid Barrier

By Burndy
Catalog # [YSU4W6W](#)



Heavy-walled AL tubing with solid barrier minimizes galvanic corrosion, Color Code:Blue (Side A), Green (Color Code)

Features

- Heavy-walled aluminum tube with solid barrier minimizes galvanic corrosion of conductors
- Accommodates neutral strands of SE Service Entrance Conductors as well as others
- Installed with standard tooling, color-coded, and pre-filled with PENETROX Joint Compound and Stripsealed

Application

Heavy-walled Aluminum tubing with solid barrier minimizes galvanic corrosion of conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size A	5 AWG, 6 AWG
Conductor - AL Str Size B	8 AWG
Conductor - AL Str Size A Range	5 AWG-6 AWG
Conductor - ACSR Str Size A	6 (6/1) Turkey AWG
Conductor - Copper Str Size A	5 AWG, 6 AWG
Conductor - Copper Str Size B	8 AWG
Conductor - Copper Str Size A Range	5 AWG-6 AWG
Conductor - Copper Solid Size A	4 AWG
Conductor - Copper Solid Size B	6 AWG

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	51 mm
Dimension - Outside Diameter inch	0.65 in
Dimension - B Length inch	0.87 in
Dimension - Length Overall inch	2 in

General

Trade Name	LINKIT™
Die Index	• 243 • BG or 5/8
Prefilled Oxide Inhibitor	Y
Plated	Y
Sub Brand	LINKIT
UPC	781810142738
Color Code - Side B	Green
Color Code - Side A	Blue
Type	Service Entrance, Uninsulated, Center Stop
Construction Material - Main Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810142738
UPC 14 Digit GTIN	00781810142738

Logistics

Minimum Pack Quantity	100
Pallet Quantity	29600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)