



Deck-mounted manual sink faucet

Series: 786

- 8" centers
- 1/2" NPSM supply inlets and coupling nut for 3/8" or 1/2" flexible riser
- Vandal-resistant handles standard
- Ceramic or Quaturn™ and Control-A-Flo compression cartridges
- Polished chrome finish



Model	Cartridge	Handle	Outlet	Spout
786-GN1AE29ABCP	Quaturn	317	E29	GN1A
786-GN1AE29VPABCP	Quaturn	317	E29VP	GN1A
786-GN1AE3ABCP	Quaturn	317	E3	GN1A
786-GN1AE3XKAB	Ceramic	317	E3	GN1A
786-GN1AE35ABCP	Quaturn	317	E35	GN1A
786-GN1FCABCP	Quaturn	317	–	GN1FC
786-E2805-5ABCP	Quaturn	317	E2805-5	GN2A
786-E2805-5VPCABCP	Quaturn	317	E2805-5	GN2A
786-E2805-5XKABCP	Ceramic	317	E2805-5	GN2A
786-E29ABCP	Quaturn	317	E29	GN2A
786-E29VPCABCP	Quaturn	317	E29VP	GN2A
786-E29XKABCP	Ceramic	317	E29	GN2A
786-TWE29ABCP*	Quaturn	317	E29	GN2A
786-TWE29XKABCP*	Ceramic	317	E29	GN2A
786-E29VPXKABCP	Ceramic	317	E29VP	GN2A
786-E3-245ABCP	Control-A-Flow	317	E3	GN2A
786-E3ABCP	Quaturn	317	E3	GN2A
786-E3XKABCP	Ceramic	317	E3	GN2A
786-TWGN2AE3ABCP*	Quaturn	317	E3	GN2A
786-TWGN2AE3XKABCP*	Ceramic	317	E3	GN2A
786-E35ABCP	Quaturn	317	E35	GN2A
786-E35XKABCP	Ceramic	317	E35	GN2A
786-TWGN2AE35ABCP*	Quaturn	317	E35	GN2A
786-E35VPCABCP	Quaturn	317	E35VP	GN2A
786-E36ABCP	Quaturn	317	E36	GN2A
786-E36XKABCP	Ceramic	317	E36	GN2A
786-E3VPCABCP	Quaturn	317	E3VP	GN2A
786-GN2AFCE1ABCP	Quaturn	317	E1	GN2AFC
786-GN2AFCABCP	Quaturn	317	–	GN2AFC
786-TWGN2AFCABCP*	Quaturn	317	–	GN2AFC
786-ABCP	Quaturn	317	E4	GN2B
786-TWABCP*	Quaturn	317	E4	GN2B
786-TWXKABCP*	Ceramic	317	E4	GN2B
786-XKABCP	Ceramic	317	E4	GN2B
786-GN2FCABCP	Quaturn	317	–	GN2FC

*Includes third-water connection

Model	Cartridge	Handle	Outlet	Spout
786-GN2FCXKABCP	Ceramic	317	–	GN2FC
786-TWGN2FCABCP*	Quaturn	317	–	GN2FC
786-TWGN2FCXKABCP*	Ceramic	317	–	GN2FC
786-GN8AE29ABCP	Quaturn	317	E29	GN8A
786-GN8AE29VPABCP	Quaturn	317	E29VP	GN8A
786-GN8AE29XKABCP	Ceramic	317	E29	GN8A
786-TWGN8AE29VXKAB*	Ceramic	317	E29VP	GN8A
786-GN8AE3ABCP	Quaturn	317	E3	GN8A
786-GN8AE3XKABCP	Ceramic	317	E3	GN8A
786-TWGN8AE3XKABCP*	Ceramic	317	E3	GN8A
786-GN8AE35ABCP	Quaturn	317	E35	GN8A
786-GN8AE36ABCP	Quaturn	317	E36	GN8A
786-GN8AE3VPCABCP	Quaturn	317	E3VP	GN8A
786-GN8AFCABCP	Quaturn	317	–	GN8AFC
786-GN8FCABCP	Quaturn	317	–	GN8FC
786-GN8FCXKABCP	Ceramic	317	–	GN8FC
786-TWGN8FCABCP*	Quaturn	317	–	GN8FC
786-L9E29ABCP	Quaturn	317	E29	L9
786-L9E36ABCP	Quaturn	317	E36	L9
786-E3-319ABCP	Quaturn	319	E3	GN2A
786-E3-319XKABCP	Ceramic	319	E3	GN2A
786-E35-319ABCP	Quaturn	319	E35	GN2A
786-GN2FC319ABCP	Quaturn	319	–	GN2FC
786-GN8AE3-319ABCP	Quaturn	319	E3	GN8A
786-E3-369ABCP	Quaturn	369	E3	GN2A
786-E3-369XKABCP	Ceramic	369	E3	GN2A
786-E35-369ABCP	Quaturn	369	E35	GN2A
786-E3-369VPAABCP	Quaturn	369	E3VP	GN2A
786-GN2FC369ABCP	Quaturn	369		GN2FC
786-GN8AE3-369ABCP	Quaturn	369	E3	GN8A
786-GN8AE3V369AB	Quaturn	369	E3VP	GN8A
786-LESHAB	Quaturn	–	–	–
786-LESHXKAB	Ceramic	–	–	–
786-TWLESHAB*	Quaturn	–	–	–