


ACCESSORIES & REPLACEMENT PARTS for warning whips

One of the benefits to using Checkers Warning Whips is having the ability to use our wide variety of mounting options that accommodate almost any need you may have. We also offer a full selection of replacement parts.

SPRING MOUNTS



Model	Description	Prop 65
FS7006	Heavy Duty Spring Mount with Bright Zinc Finish for Lighted Models in 3 ft to 8 ft lengths (Includes Lock Washer and Jam Nut)	-
FS7006-DUD	Heavy Duty Spring Mount with Bright Zinc Finish for Lighted Models in 3 ft to 8 ft lengths (Includes Lock Washer and Jam Nut)	-
FS7006U	Heavy Duty Spring Mount with Bright Zinc Finish for Lighted Models in 3 ft to 8 ft lengths (Includes Lock Washer and Jam Nut)	-
FS7006U-DUD	Heavy Duty Spring Mount with Bright Zinc Finish for Lighted Models in 3 ft to 8 ft lengths (Includes Lock Washer and Jam Nut)	-

ASSORTED MOUNTS

Model	Description	Prop 65
FS7010-1.5	Billet, Fold-Down, Clamp Mount Bracket for 1.5 in. Round Tubing	-
FS7010-1.75	Billet, Fold-Down, Clamp Mount Bracket for 1.75 in. Round Tubing	-
FS7012	Aluminum "L" Bracket Mount (Mounting Hardware Included)	-
FS7014-1.75	Billet, Fold-Down, Clamp Mount Bracket for 1.75 in. Round Tubing	-
FS7016	Billet, Fold-Down, Tab Mount Bracket	-
FS7017	12 Ga. Black Powder-Coated Steel, Flat Surface Mounting Bracket	-
FS7018	Steel Fire Hydrant/Flange Mount with Bright Zinc Finish	-
FS7019	Aluminum tube style mirror bracket for 1/2 in. to 1 in. OD. (Mounting hardware included)	-
FS7050	Steel Stake Mount with Bright Zinc Finish	-
VIATBPH	TEMPORARY mount for truck bed post holes	-
RRMSW	Aluminum Roof Rack with fold-down mounting bracket with strobe light and 5 ft. Super Whip.	-
WDRS	Steel Fold Down Whip Retainer Bracket, Black Powder Coated with Three 1/4 in. Universal Mounting Holes. Quickly Fastens Whips Down (Mounting Hardware NOT Included)	-
TPFLATMOUNT	Flat Mount Bracket with Mounting Holes	-
VIAMOUNT-F	Steel Quick Release Fold Down Mounting Bracket, Black Powder Coated with Stainless Steel Hardware (Mounting Hardware NOT Included)	-
VIAMOUNT	Steel "I" Mounting Bracket, Black Powder Coated with Four 1/4 in. Universal Mounting Holes and 1/2 in. Hole for Attaching Whip (Mounting Hardware NOT Included)	-
VIAMOUNT-S	Steel "I" Mounting Bracket, Black Powder Coated with Four 1/4 in. Universal Mounting Holes and 1/2 in. Slit for Attaching Whip (Mounting Hardware NOT Included)	-
FS3000	Replacement Compression Hex Base Mount - ONLY for Light Duty Non-Lighted Whips	-
FS3009LD	Magnetic Mounting Base - ONLY for Light Duty Non-Lighted Whips up to 7 ft.	-
FS7009	Magnetic Mount Base with Handle	-
FS7009PCS	Magnetic Mount Base w/ Handle & 7 ft. Coiled Power Cord w/ Switch-On Lighter Plug	-
FS3009LD	Magnetic Mounting Base - ONLY for Light Duty Non-Lighted Whips up to 7 ft.	-
FS7009	Magnetic Mount Base with Handle	-
FS7009PCS	Magnetic Mount Base w/ Handle & 7 ft. Coiled Power Cord w/ Switch-On Lighter Plug	-



*RECOMMENDED FOR USE WITH 3 & 5 FT. WHIPS AND ARE FOR TEMPORARY USE ONLY