

Ref. No.	Description	75 Ton Part No.	1.0 Ton Part No.	1.5 Ton Part No.	Qty
1	Pinion Shaft	IRB5001	IRB5001	KRB5001	1
2	Pinion with Pinion Gear	IRB4002T	IRB4002T	KRB4002T	2
3	Load Gear	IRB4004	JRB4004	KRB5004	1
4	Load Sheave	IRB5005	IRB5005	KRB5005	1
†5	Load Chain	T56	V56	V71	1
6	Pawl	IRB5007	IRB5007	KRB5007	2
7	Disc Hub	IRB5008	IRB5008	KRB5008	1
8	Ratchet Wheel	IRB5009	IRB5009	KRB5009	1
9	Chain Guide	IRB5012	IRB5012	KRB5012	2
10	Stripper	IRB5015	IRB5015	KRB5015	1
11	Stop Grip	IRB40062T	IRB40062T	KRB40062T	1
12	Gear Side Plate	IRB5018T	IRB5018T	KRB5018T	1
13	Handle Side Plate	IRB5020U	IRB5020U	KRB5020U	1
14	Disc Nut	IRB5023A	IRB5023A	KRB5023A	1
15	Operating Handle	IRB5024T	IRB5024T	KRB5024T	1
16	Spring Shaft	IRB4030	IRB4030	IRB3030	1
17	Shaft Base	IRB4031	IRB4031	IRB3031	1
18	Handle Pawl	GRB5032	GRB5032	KRB5032	1
19	Gear Cover	IRB5037	IRB5037	KRB5037	1
20	Ratchet Cover Assembly	IRB5040	IRB5040	KRB5040	1
21	Guide Handle	IRB5042	IRB5042	IRB5042	1
22	Top Hook Assembly	IRB5048U	JRB5048U	KRB5048U	1
23	Yoke Pin	IRB5051	IRB5051	KRB5051	1
24	Bottom Hook Assembly	IRB5053U	JRB5053U	KRB5053U	1
25	Collar for Pinion Shaft	IRB5059	IRB5059	IRB5059	1
26	Hook Latch Assembly	GRB5074T	JRB5074T	KRB5074T	2
27	Change Over Spring	IRB4101	IRB4101	IRB3116	1
28	E-Ring	SRE8	SRE8	SRE9	2
29	Pawl Spring	IRB5104	IRB5104	KRB5104	2
30	Brake Lining	IRB5105	IRB5105	KRB5105	2
31	Free-Chaining Spring	IRB5106	IRB5106	KRB5106	1
32	Spring Nut	HSN1M8	HSN1M8	HSN1M8	8
33	Spring Nut	HSN1M6	HSN1M6	HSN1M8	2
34	Upset Bolt	CUSM6X10S2	CUSM6X10S2	CUSM8X12S2	1
35	Name Plate	IRB5114DN	JRB5114DN	KRB5114DN	1
36	Plain Washer	PWM8M	PWM8M	PWM8M	1
37	Nylon Nut	HNN1M8	HNN1M8	HNN1M8	1
*38	Chain Fastening Bolt	IRB4124T	IRB4124T	KHH5048T	1
39	Cross Recessed Head Bolt	CBM5X25B3	CBM5X25B3	CBM5X25B3	2
40	Warning Label	IRB4146DN	IRB4146DN	IRB4146DN	1

† Specify the lift when placing an order for Load Chain.

* Includes Nut and Bolt.

NOTE: When ordering spare parts please have Model, Capacity, Product Number and Quantity available