


Industrial Wireway



Wireway Size Listed left of dash (-)

Wireway Type Immediately follows dash (-)

12	NEMA 12
4X	NEMA 4X
4XS	NEMA 4X Type 304 Stainless Steel

Wireway Styles Immediately follows Type designation

FW	Feed-Through Wireway
LW	Lay-In Wireway
WT	Wiring Trough

Lay-In Wireway Fittings

LAHM	Adapter for Hammond [†] Mfg.
LAHW	Adapter for Hoffman [†] or Wiegmann [†]
LARR	Adapter for Robroy [†] or Rittal [†]
LASD	Adapter for Square D [†]
BK	Barrier Kit
C	Coupling
LBC	Box Connector
LBH	Hanger, Bracket
LC	Cross, Top Open
LCF	Cut-Off Fitting/Lay-in Style
LCP	Closure Plate
LDH	Hanger, Drop
LE9A	90° Elbow, Top Open
LE9AC	90° Elbow, Outside-Top Open
LE9B	90° Elbow, Inside Open
LE9C	90° Elbow, Outside Open
LE9TC	90° Transposition Elbow, CW
LE9TCC	90° Transposition Elbow, CCW
LE15A	15° Elbow, Top Open
LE45A	45° Elbow, Top Open
LE45B	45° Elbow, Inside Open
LE45C	45° Elbow, Outside Open
LJB	Junction Box
LN1	1" Nipple
LN2	2" Nipple
LN3	3" Nipple
LR	Reducer
LSP	Sealing Plate, Flat
LTA	Tee, Top Open
LTF	Telescopic Fitting
LTSC	Transposition, Clockwise
LTSCC	Transposition, Counter Clockwise

[†] Marks shown are property of respective owners.

Feed-Through Fittings

BH	Hanger, Bracket
BK	Barrier Kit
DH	Hanger, Drop
FBC	Box Connector
FC	Cross
FCF	Cut-Off Fitting
FCP	Closure Plate
FE9	90° Elbow
FE45	45° Elbow
FFF	Flexible Fitting
FGK	Gasket Kit
FN1	1" Nipple
FN2	2" Nipple
FN3	3" Nipple
FN6	6" Nipple
FRC	Reducer Center
FRE	Reducer Edge
FT	Tee
FTF	Telescopic Fitting

Commercial Wireway



Wireway Size Listed First

Screw Cover Wireway Style Follows Size designation

G	Type 1 Screw Cover Wireway
GGV	Type 1 Screw Cover Wireway Galvanized

Screw Cover Wireway Fittings

C	Wireway Connector
E	Wireway End
FH	Wireway Hanger
FL	Hinged Elbow
FR	Wireway Reducer
FTF	Telescopic Fitting
GF	Wireway End Flange
L	Elbow
L SWEEP	Sweep Elbow
LTX	Elbow-Tee-Cross
T	Wireway Tee
X	Wireway Cross