

## Sleeve Type Expansion Anchors

UPC/Part Number	Catalog Number	Size	Thread Length	Box Qty.
<b>Hex Nut Style</b>				
78101102995	<b>ASA-37-187HN</b>	3/8" x 1 7/8"	1 5/8"	50
78101102996	<b>ASA-37-300HN</b>	3/8" x 3"	1 5/8"	50
78205153400	<b>ASA-37-400HN</b>	3/8" x 4"	1 5/8"	50
78101102997	<b>ASA-50-225HN</b>	1/2" x 2 1/2"	2 1/8"	25
78101102998	<b>ASA-50-300HN</b>	1/2" x 3"	2 1/4"	25
78101102999	<b>ASA-50-400HN</b>	1/2" x 3 3/4"	2 1/4"	25
78205153351	<b>ASA-50-525HN</b>	1/2" x 5 1/4"	2 1/4"	25
78101103002	<b>ASA-50-600HN</b>	1/2" x 6"	2 1/4"	10
78101103003	<b>ASA-62-225HN</b>	5/8" x 2 1/2"	2 1/8"	25
78101103004	<b>ASA-62-300HN</b>	5/8" x 3"	2 3/4"	25
78101103005	<b>ASA-62-425HN</b>	5/8" x 4 1/4"	2 3/4"	10
78101103006	<b>ASA-62-600HN</b>	5/8" x 5 3/4"	2 3/4"	10
78101103007	<b>ASA-75-250HN</b>	3/4" x 2 3/4"	2 1/8"	10
78101103008	<b>ASA-75-425HN</b>	3/4" x 4 1/4"	3 3/8"	10
78101103009	<b>ASA-75-625HN</b>	3/4" x 6 1/4"	3 3/8"	10

**Hex Nut Style - Stainless Steel**

78205153343	<b>ASA-37-187HNSS4</b>	3/8" x 1 7/8"	1 5/8"	50
78205153345	<b>ASA-37-300HNSS4</b>	3/8" x 3"	1 5/8"	50
78205153347	<b>ASA-50-225HNSS4</b>	1/2" x 2 1/2"	2 1/8"	25
78205153349	<b>ASA-50-300HNSS4</b>	1/2" x 3"	2 1/4"	25
78205153350	<b>ASA-50-400HNSS4</b>	1/2" x 3 3/4"	2 1/4"	25
78205153352	<b>ASA-62-425HNSS4</b>	5/8" x 4 1/4"	2 3/4"	10

**Acorn Nut Style**

78205153341	<b>ASA-25-62AN</b>	1/4" x 5/8"	1/2"	100
78101102991	<b>ASA-25-137AN</b>	1/4" x 1 3/8"	1 1/8"	100
78101102992	<b>ASA-25-225AN</b>	1/4" x 2 1/4"	1 1/8"	100

**Slotted Round Head Style**

78205153338	<b>ASA-25-112RS</b>	1/4" x 1 3/8"	1"	100
78205153340	<b>ASA-25-200RS</b>	1/4" x 2 1/4"	1 1/8"	100

UPC/Part Number	Catalog Number	Size	Drill Diameter	Box Qty.
<b>Rod Hanger</b>				
78205153339	<b>ASA-25-150RH</b>	1/4" x 1 1/2"	5/16"	50
78205153344	<b>ASA-37-187RH</b>	3/8" x 1 7/8"	3/8"	50
78205153348	<b>ASA-50-225RH</b>	1/2" x 2 1/4"	1/2"	25
<b>Wire Hanger</b>				
78205153342	<b>ASA-31-150WH</b>	5/16" x 2 3/8"	5/16"	100

Read safety/installation instruction sheets in packages before use.