


Runway Supports

- Strong welded steel construction
- Provides a pathway for backbone and horizontal cable runs
- Full range of splicing and support accessories available

Runway Supports


Part Number	Description	OPA Number
**	Typical Ceiling Supports for Runway 6" -36"	OPA-2452-07
**	Typical Wall Supports for Runway 6" -36"	OPA-2454-07
SB213AL06K	Wall Bracket for 6" Runway	OPA-2453-07
SB213AL12K	Wall Bracket for 12" Runway	OPA-2453-07
SB213AL18K	Wall Bracket for 18" Runway	OPA-2453-07

**See full catalog (BLCOMD-12) for a complete list of part numbers for these items.



Two-Post Racks

- Double sided universal mounting spacing
- Standard finish flat black powder coat
- Full range of shelves, cable management, and accessories available



Two-Post Racks

Part Number	Description	OPA Number	OPA Number with Gusset Kit
3" Channel			
SB556036XU	Two-post rack, 19" wide, 3" channel, 36" tall	OPA-2426-10	OPA-2853-10
SB556048XU	Two-post rack, 19" wide, 3" channel, 48" tall	OPA-2426-10	OPA-2853-10
SB556072XU	Two-post rack, 19" wide, 3" channel, 72" tall	OPA-2426-10	OPA-2853-10
SB556084XU	Two-post rack, 19" wide, 3" channel, 84" tall	OPA-2426-10	OPA-2853-10
SB556096XU	Two-post rack, 19" wide, 3" channel, 96" tall	OPA-2426-10	OPA-2853-10
SB556108XU	Two-post rack, 19" wide, 3" channel, 108" tall	OPA-2426-10	OPA-2853-10
SB558036XU	Two-post rack, 23" wide, 3" channel, 36" tall	OPA-2426-10	OPA-2853-10
SB558048XU	Two-post rack, 23" wide, 3" channel, 48" tall	OPA-2426-10	OPA-2853-10
SB558072XU	Two-post rack, 23" wide, 3" channel, 72" tall	OPA-2426-10	OPA-2853-10
SB558084XU	Two-post rack, 23" wide, 3" channel, 84" tall	OPA-2426-10	OPA-2853-10
SB558096XU	Two-post rack, 23" wide, 3" channel, 96" tall	OPA-2426-10	OPA-2853-10
SB558108XU	Two-post rack, 23" wide, 3" channel, 108" tall	OPA-2426-10	OPA-2853-10
6" Channel			
SB556608419U6	Two-post rack, 19" wide, 6" channel, 84" tall	OPA-2427-10	
SB556608423U6	Two-post rack, 24" wide, 6" channel, 84" tall	OPA-2427-10	
SB556608435U6	Two-post rack, 36" wide, 6" channel, 84" tall	OPA-2427-10	
Seismic			
SB85219084	Two-post seismic rack, 19" wide, 84" tall	OPA-2430-07	
SB85223084	Two-post seismic rack, 23" wide, 84" tall	OPA-2430-07	
SB85219096	Two-post seismic rack, 19" wide, 96" tall	OPA-2779-10	
SB85223096	Two-post seismic rack, 23" wide, 96" tall	OPA-2779-10	